

## Single Phase Glass Passivated Silicon Bridge Rectifier

$V_{RRM} = 50 \text{ V} - 400 \text{ V}$

$I_O = 4 \text{ A}$

### Features

- Plastic package has Underwriters Laboratory Flammability Classification 94V-0
- High case dielectric strength of 1500  $V_{RMS}$
- Glass passivated chip junction
- Ideal for printed circuit boards
- High surge overload rating
- High temperature soldering guaranteed: 260°C/ 10 seconds, 0.375 (9.5mm) lead length
- Not ESD Sensitive


### Mechanical Data

Case: Molded plastic body over passivated junctions

Terminals: Plated leads, solderable per MIL-STD-750 Method 2026.

Mounting position: Any

GBU Package



### Maximum ratings at $T_c = 25^\circ\text{C}$ , unless otherwise specified

Parameter	Symbol	Conditions	GBU4A	GBU4B	GBU4D	GBU4G	Unit
Repetitive peak reverse voltage	$V_{RRM}$		50	100	200	400	V
RMS reverse voltage	$V_{RMS}$		35	70	140	280	V
DC blocking voltage	$V_{DC}$		50	100	200	400	V
Operating temperature	$T_j$		-55 to 150	-55 to 150	-55 to 150	-55 to 150	$^\circ\text{C}$
Storage temperature	$T_{stg}$		-55 to 150	-55 to 150	-55 to 150	-55 to 150	$^\circ\text{C}$

### Electrical characteristics at $T_c = 25^\circ\text{C}$ , unless otherwise specified

Single phase, half sine wave, 60 Hz, resistive or inductive load







For capacitive load derate current by 20%

Parameter	Symbol	Conditions	GBU4A	GBU4B	GBU4D	GBU4G	Unit
Maximum average forward rectified current <sup>1,2</sup>	$I_O$	$T_c = 100^\circ\text{C}$	4.0	4.0	4.0	4.0	A
Peak forward surge current	$I_{FSM}$	$t_p = 8.3 \text{ ms}$ , half sine	150	150	150	150	A
Maximum instantaneous forward voltage drop per leg	$V_F$	$I_F = 4 \text{ A}$	1.1	1.1	1.1	1.1	V
Maximum DC reverse current at rated DC blocking voltage per leg	$I_R$	$T_a = 25^\circ\text{C}$	5	5	5	5	$\mu\text{A}$
		$T_a = 125^\circ\text{C}$	500	500	500	500	$\mu\text{A}$
Rating for fusing	$I^2t$	$t < 8.3 \text{ ms}$	93	93	93	93	$\text{A}^2\text{sec}$
Typical junction capacitance per leg <sup>3</sup>	$C_j$		100	100	100	100	pF
Typical thermal resistance per leg <sup>1,2</sup>	$R_{\theta JA}$		22	22	22	22	$^\circ\text{C/W}$
	$R_{\theta JL}$		4.2	4.2	4.2	4.2	$^\circ\text{C/W}$

<sup>1</sup> - Device mounted on 40 mm x 40 mm x 1.5 mm Al plate heatsink

<sup>2</sup> - Recommended mounted position is to bolt down device on a heatsink with silicon thermal compound for maximum heat transfer using #6 screw.


<sup>3</sup> - Measured at 1.0 MHz and applied reverse bias of 4.0 V



## Package dimensions and terminal configuration

Product is marked with part number and terminal configuration.

## GBU



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[GeneSiC Semiconductor:](#)

[GBU4B](#)