

# Bulk tubular non-metallic braid for wire harness protection

## 102-071 tubular braid, Kevlar®



Natural

**B**  
Black


- Yarn, duPont™ Kevlar® tubular braid
- -73° to +160°C temperature range
- 400,000 PSI yield tensile strength
- 3.6% elongation
- Excellent chemical resistance
- Good abrasion resistance
- Fire-resistant, will not melt

How To Order			
Sample Part Number	102-071	-008	B
Basic No.	Tubular braid, Kevlar®		
Braid Diameter No.	See Table I		
Color option	B = Black    Omit for Natural		

Table I			
Part No.	Nominal I.D.	Wire Bundle Accommodation Range Ref.	
		Min.	Max.
-004	.125 (3.2)	.090 (2.3)	.250 (6.4)
-008	.250 (6.4)	.125 (3.2)	.375 (9.5)
-012	.375 (9.5)	.312 (7.9)	.500 (12.7)
-016	.500 (12.7)	.250 (6.4)	.750 (19.1)
-024	.750 (19.1)	.500 (12.7)	1.250 (31.8)
-032	1.250 (31.8)	.625 (15.9)	1.375 (34.9)
-040	1.250 (31.8)	.750 (19.1)	1.500 (38.1)
-064	2.000 (50.8)	1.375 (34.9)	2.500 (63.5)



*Non-metallic tubular braid, Kevlar®, earns much of its reputation for strength and abrasion resistance due to its construction from individual strands of yarn (as opposed to monofilament materials such as FEP and PEEK). 102-071 is Glenair's strongest non-metallic tubular braid material, and offers excellent resistance to caustic chemicals and fluids as well as wire interconnect protection at temperatures up to 160°C.*

### NOTES

1. Material - DuPont™ Kevlar®, natural or black.  
DuPont™ and Kevlar® are trademarks or registered trademarks of E.I. duPont de Nemours and Company.
2. Minimum order length is 100 ft. (30.5m)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[102-071-040](#) [102-071-016](#) [102-071-024](#) [102-071-048](#) [102-071-032](#) [102-071-004](#) [102-071-064](#)