

**CONNECTOR
DESIGNATOR
A-F-H-L-S
SELF-LOCKING
ROTATABLE
COUPLING**

Product Series — **620 F B 049 M 16 D**
Connector Designator —
Angle and Profile —
 B = 45°
Basic Part No. —
Drain Hole Option
(Omit for None)
Shell Size
Finish (Table II)




TABLE III: CABLE ENTRY

Shell Size	E Max	F Max	Cable Entry	
			Closed	Open
08/09	1.536 (39.0)	.730 (18.5)	.125 (3.2)	.204 (5.2)
10/11	1.566 (39.8)	.810 (20.6)	.187 (4.7)	.286 (7.3)
12/13	1.646 (41.8)	.870 (22.1)	.291 (7.4)	.416 (10.6)
14/15	1.686 (42.8)	.930 (23.6)	.351 (8.9)	.476 (12.1)
16/17	1.796 (45.6)	.990 (25.1)	.501 (12.7)	.626 (15.9)
18/19	1.906 (48.4)	1.110 (28.2)	.518 (13.2)	.706 (17.9)
20/21	1.956 (49.7)	1.170 (29.7)	.581 (14.8)	.831 (21.1)
22/23	1.996 (50.7)	1.240 (31.5)	.644 (16.4)	.956 (24.3)
24/25	2.046 (52.0)	1.300 (33.0)	.706 (17.9)	1.081 (27.5)

**See inside back cover
fold-out or pages 13 and
14 for Tables I and II.**

1. Cable Entry is defined as the accommodation entry for the wire bundle or cable. Dimensions are not intended for inspection criteria.
2. Metric dimensions (mm) are indicated in parentheses.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[620HB049NF25](#) [620HS048NF15](#) [620HS048NF17](#) [620HB049M11](#) [620HB049NF11](#) [620HB049NF13](#)
[620HB049NF17](#) [620HB049NF19](#) [620HB049NF21](#) [620HB049NF23](#) [620HS048M09](#) [620HS048M17](#) [620HS048N15](#)
[620HB049B19](#) [620HB049NF15](#) [620HB049B17](#) [620HB049M25](#) [620HB049NF09](#) [620HB049M09](#) [620HB049M13](#)
[620HB049M15](#) [620HB049NF19D](#) [620HB049N25](#) [620FB049N24](#) [620FB049N10](#) [620FB049N22](#) [620HB049M23](#)
[620HB049NF15D](#) [620AB049C12](#)