



HIGH-TEMPERATURE TOLERANT ThermaRex HT Series 79 Micro-D Connectors with Micro-Crimp Contacts


How To Order / Contact Arrangements



How To Order ThermaRex Series 79 connectors				
Sample Part Number	797	-756	S	H-29P7
Series / Basic Part No.	797 High-temperature ThermaRex Series 79 crimp-contact rectangular			
Connector Type	-756 = Plug -757 = Receptacle			
Contact Type	S = Socket (for -756 Plug connectors) P = Pin (for -757 Receptacle connectors)			
Insert Arrangement	Per 799-009. See insert arrangement tables below			


- Service rating up to 300°C
- Vibration-resistant jackpost coupling
- High-temperature ceramic insulators and silicone seals
- Durable stainless steel construction

ThermaRex High-Temperature Crown Ring Contact Arrangements (pin mating face shown)				
A-5 5 #23	B-2P2 / B-2W2 2 #16	B-9 9 #23	C-13 13 #23	D-15 15 #23
D-3P3 / D-3W3 3 #16	D-7P2 / D-7W2 5 #23 / 2 #16	E-11P2 / E-11W2 9 #23 / 2 #16	E-19 19 #23	
E-7P3 / 4 #23 3 #16	F-15P2 / F-15W2 13 #23 / 2 #16	F-23 23 #23		
F-5P5 / F-5W5 5 #16	G-33 33 #23			
H-10P4 / H-10W4 6 #23 / 4 #12	H-29P7 22 #23 / 7 #16			
H-36P2 / H-36W2 34 #23 / 2 #12	H-54P2 / H-54W2 52 #23 / 2 #16			



HIGH-TEMPERATURE TOLERANT ThermaRex HT Series 79 Micro-D Connectors with Micro-Crimp Contacts

How To Order / Contact Arrangements



MATERIAL / FINISH NOTES

Housing, Float Mount Hardware, Guide Socket - Stainless Steel / Passivated
Pin and Socket Contact - Copper Alloy / Gold Plated
Socket Hood - Stainless Steel / Passivated
Insulators - High Grade Ceramic / N/A
Grommet and Interfacial Seal - High Temperature Silicone / N/A
Retainer Clip Stainless Steel / N/A
EMI Spring - Stainless Steel / Gold Plated

ELECTRICAL PERFORMANCE

Contacts: Size 23 = 5 Amps Max. / Size 16 = 13 Amps Max./ Size 12 = 23 Amps Max.
DWV - 500 Vac, with 5 Milliampere Max.leakage
Insulation Resistance - 5,000 Megohms Max.

Operating Temperature: -65°C to +300°C

BLIND MATE MISALIGNMENT ALLOWANCE

Shell Sizes A, B, C, D, E, F, G, J, K:
 ± 0.040 (1.02) Allowable misalignment from centerline
Shell Sizes H, L:
 ± 0.040 (1.02) Allowable misalignment from centerline
Shell Size M:
 ± 0.050 (1.27) allowable misalignment from centerline

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[797-075PG-33MSS](#) [797-240PH-3P3MP](#) [797-257](#) [797-522SJ-17P4MEPB](#)