




Series 805 Mighty Mouse Triple-Start ACME Thread Jam-Nut, Rear Panel Mount PCB Receptacle 805-067 Ordering Information



Series 805 Jam-Nut, Rear Panel Mount Printed Circuit Board Receptacle features a choice of stainless steel or aluminum alloy shells. Threaded heli-coil (2-56 x .086) allows for direct to board attachment. Available PC tail or solder cup contacts are gold plated copper alloy and non-removable. Integral .025 (0.64) standoff

allows for board washout. Choose PC tails for attachment to flexible or rigid boards. Select solder cups for direct wire attachment. Connector is back potted and paralyene compatible. Mates with all triple start threaded high density series 805 plug connectors with the same polarization and opposite contact gender.

How To Order

Sample Part Number		805-067	-07	M	8-23	P	A
Series	805-067 = PCB Receptacle with Solder Cup or PC tail Contacts						
Shell Style (See Table I)	-07 = Jam-Nut, Rear Panel Mount Receptacle with Non-Locking Heli-Coils -17 = Jam-Nut, Rear Panel Mount Receptacle with Self-Locking Heli-Coils						
Shell Material and Finish	C = Aluminum / Black Anodize (Non-Conductive); RoHS Compliant M = Aluminum / Electroless Nickel; RoHS Compliant MT = Aluminum / Nickel-PTFE RoHS Compliant NF = Aluminum / Cadmium with Olive Drab Chromate ZNU = Aluminum / Zinc-Nickel with Black Chromate Z1 = Stainless Steel / Passivated; RoHS Compliant						
Shell Size - Insert Arrangement	See Contact Arrangements Page H-2						
Contact Type	P = Pin, PC Tail E = Pin, Solder Cup S = Socket, PC Tail F = Socket, Solder Cup						
Polarization (See Table II)	A = Normal B = Pos. B C = Pos. C D = Pos. D E = Pos. E F = Pos. F						

Table I: Shell Style

-07 Jam-Nut, Rear Panel Mount with Non-Locking Heli-Coils	-17 Jam-Nut, Rear Panel Mount with Self-Locking Heli-Coils

Table II: Keyway Positions

Position	A°	B°
A (Normal)	150°	210°
B	75°	210°
C	95°	230°
D	140°	275°
E	75°	275°
F	95°	210°

NOTES

1. Contacts are nonremoveable and connector is back potted
2. Connector receptacle mates with all series 805 triple start threaded high density plug connectors with same polarization and opposite contact gender
3. For all #8 arrangements, add .227 (5.77) to overall length


Dimensions in Inches (millimeters) are subject to change without notice.

Series 805 Mighty Mouse Triple-Start ACME Thread Square Flange Jam-Nut PCB Receptacle 805-067 Shell Style -07 Dimensions



Series 805

Jam-nut, rear panel mount receptacle - shell style 07



Dimensions							
Shell Size	A Thread	B Thread	C Flat	Ø D	E SQ	F BSC	G Typ
8	.5000-1P-.3L-TS	.5625-28 UNEF-2A	.535 (13.59)	.920 (23.37)	.729 (18.52)	.496 (12.60)	.276 (7.01)
9	.5625-1P-.3L-TS	.6875-28 UN-2A	.661 (16.79)	1.110 (28.19)	.859 (21.82)	.627 (15.93)	.407 (10.34)
10	.6250-1P-.3L-TS	.6875-28 UN-2A	.661 (16.79)	1.110 (28.19)	.859 (21.82)	.627 (15.93)	.407 (10.34)
11	.6875-1P-.3L-TS	.7500-28 UN-2A	.721 (18.31)	1.200 (30.48)	.930 (23.62)	.698 (17.73)	.478 (12.14)
12	.7500-1P-.3L-TS	.8125-28 UN-2A	.784 (19.91)	1.370 (34.80)	1.044 (26.52)	.812 (20.62)	.592 (15.04)
13	.8125-1P-.3L-TS	.8750-28 UN-2A	.843 (21.41)	1.420 (36.07)	1.085 (27.56)	.853 (21.67)	.633 (16.08)
15	.9375-1P-.3L-TS	1.0000-28 UN-2A	.970 (24.64)	1.560 (39.62)	1.175 (29.85)	.943 (23.95)	.723 (18.36)
18	1.1250-1P-.3L-TS	1.1875-28 UN-2A	1.147 (29.13)	1.800 (45.72)	1.351 (34.32)	1.119 (28.42)	.899 (22.83)
19	1.1875-1P-.3L-TS	1.2500-28 UN-2A	1.221 (31.01)	1.880 (47.75)	1.407 (35.74)	1.175 (29.85)	.955 (24.26)
21	1.3125-1P-.3L-TS	1.3750-28 UN-2A	1.350 (34.29)	2.090 (53.09)	1.550 (39.37)	1.318 (33.48)	1.098 (27.89)
23	1.4375-1P-.3L-TS	1.5000-28 UN-2A	1.470 (37.34)	2.270 (57.66)	1.680 (42.67)	1.448 (36.78)	1.228 (31.19)

Jam-Nut Panel Cutout		
Shell Size	H Flat	Ø J
8	.545 (13.84) .541 (13.74)	.572 (14.53) .567 (14.40)
9	.671 (17.04) .667 (16.94)	.698 (17.73) .693 (17.60)
10	.671 (17.04) .667 (16.94)	.698 (17.73) .693 (17.60)
11	.731 (18.57) .727 (18.47)	.760 (19.30) .755 (19.18)
12	.794 (20.17) .790 (20.07)	.822 (20.88) .817 (20.75)
13	.851 (21.62) .847 (21.51)	.885 (22.48) .881 (22.38)
15	.980 (24.89) .976 (24.79)	1.010 (25.65) 1.005 (25.53)
18	1.157 (29.39) 1.153 (29.29)	1.198 (30.43) 1.193 (30.30)
19	1.231 (31.27) 1.227 (31.17)	1.260 (32.00) 1.255 (31.88)
21	1.358 (34.49) 1.354 (34.39)	1.383 (35.13) 1.381 (35.08)
23	1.480 (37.59) 1.476 (37.49)	1.510 (38.35) 1.505 (38.23)

Material and Finish

- Shell, jam-nut: aluminum alloy or SST / see how to order table
- Insulator: LCP / N.A.
- Interfacial seal, O-ring, peripheral seal: fluorosilicone / N.A.
- Contact: copper alloy / gold plate per ASTM B 488, Type II, Code C, Class 1.25, over suitable underplate
- Potting compound: epoxy / N.A.

Dimensions in Inches (millimeters) are subject to change without notice.

© 2014 Glenair, Inc.

Series 80 Mighty Mouse

U.S. CAGE Code 06324

Printed in U.S.A.

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912
www.glenair.com H-29 E-Mail: sales@glenair.com

Rev. 06.04.19

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[805-067-07NF10-28SA](#) [805-067-07NF10-2SA](#) [805-067-07NF9-10SA](#)