


Series 970 PowerTrip™ Connectors and Accessories

Receptacle Connectors

970-003 Square Flange Receptacle



Receptacle
Connectors

970-003 REAR PANEL MOUNT, SQUARE FLANGE RECEPTACLE



Series 970 PowerTrip™ extreme environment receptacle connectors are intended for high current applications where size 8 AWG to size 1/0 AWG wires are used. These connectors feature high current LouverBand contacts. Coupling threads are triple-start ACME type. EMI protected with ground spring on mating plug and splined backshell interface. Standard contacts are silver plated high conductivity copper alloy, or choose gold-plated contacts for improved corrosion protection. Fluorosilicone rubber gaskets and grommet provide watertight sealing. Contacts are packaged with connector.

- EMI Protected
- High Current Contacts
- Submersible
- Harsh Environment

PRODUCT FACTS

2000 VAC Sea Level DWV Rating
 -65°C to +200°C Operating Temperature
 6 Feet Water Immersion, 48 Hours
 65 dB min. Attenuation, up to 10GHz
 500 Cycles Mating Durability
 MIL-S 901 Grade A High-Impact Shock
 43 g Random Vibration

HOW TO ORDER

SERIES	SHELL MATL AND FINISH	SHELL SIZE - INSERT ARRANGEMENT						CONTACT TYPE AND PLATING	MOUNTING HOLE OPTION	KEY POSITION	
970-003 Square Flange Panel Mount Receptacle with Crimp Contacts	ME Aluminum, Electroless Nickel Finish	Contact Size and Qty						P1 Pin Contacts, Silver Plating*	N Thru-Hole T Clinch Nuts Installed in Mounting Holes for Back Panel Mounting.	-1 Position 1	
		Contact Arr.	#16	#12	#8	#4	#1/0				
		18-2			2					P2 Pin Contacts, Gold Plating	-2 Position 2
		18-4		2	2						
	20-3			3			S1 Socket Contacts, Silver Plating*	-3 Position 3			
	20-4			4							
	20-5		2	3				S2 Socket Contacts, Gold Plating		-4 Position 4	
	20-7	4		3							
	24-2				2		A Pin Connector, without Contacts			-5 Position 5	
	24-3				3						
	24-5			5				B Socket Connector, without Contacts		-6 Position 6	
	24-6		4		2						
	24-A6		3		3		* Size 12 and 16 contacts are gold-plated. Size 8, 4 and 1/0 are silver plated.				
	28-4				4						
	28-8		1	7							
	28-9	5			4						
	28-15	15									
	32-2					2					
	32-3					3					
	32-4				2	2					
32-5				5							
32-6		3			3						
32-20	1	19									
36-4					4						
36-16	3		13								
40-5					5						
40-21			21								
Sample Part Number											
970-003	MT	24-5						P1	N	-1	




Series 970 PowerTrip™ Connectors and Accessories

Receptacle Connectors


970-003 Square Flange Receptacle

970-003 REAR PANEL MOUNT, SQUARE FLANGE RECEPTACLE



DIMENSIONS

Shell Size	A		B Mating Thread	C Accessory Thd	D		Ø E		E Clinch Nut Thd	Ø F	
	In.	mm.			In.	mm.	In.	mm.		In.	mm.
18	1.383	35.13	1.125-.1P-.3L-TS-2A	1.125-18 UNEF-2A	1.015	25.78	.146	3.71	6-32 UNC-2B	1.187	30.15
20	1.508	38.30	1.250-.1P-.3L-TS-2A	1.250-18 UNEF-2A	1.140	28.96	.146	3.71	6-32 UNC-2B	1.374	34.90
24	1.718	43.64	1.500-.1P-.3L-TS-2A	1.4375-18 UNEF-2A	1.281	32.54	.146	3.71	6-32 UNC-2B	1.562	39.67
28	2.138	54.31	1.750-.1P-.3L-TS-2A	1.8125-16 UN-2A	1.568	39.83	.170	4.32	8-32 UNC-2B	1.835	46.61
32	2.328	59.13	2.000-.1P-.3L-TS-2A	2.0625-16 UNS-2A	1.734	44.04	.170	4.32	8-32 UNC-2B	2.093	53.16
36	2.578	65.48	2.250-.1P-.3L-TS-2A	2.250-16 UN-2A	1.984	50.39	.170	4.32	8-32 UNC-2B	2.302	58.47
40	2.828	71.83	2.500-.1P-.3L-TS-2A	2.500-16 UN-2A	2.234	56.74	.170	4.32	8-32 UNC-2B	2.562	65.07



KEY POSITIONS

Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[970003MT20-7P1N-1](#) [970003MT18-2S2T-1](#) [970003MT28-4P1N-2](#) [970-003NF32-3S2N-1](#) [970-003NF20-4S1N-1](#)
[970-003ME28-4S1T-5](#) [970-003MT18-4AN-4](#) [970-003MT20-3S2T-1](#) [970-003MT20-4S2N-6](#) [970-003MT20-5BN-6](#) [970-](#)
[003MT20-7S2N-4](#) [970-003NF24-2P2T-2](#) [970-003NF24-3P2N-1](#) [970-003NF32-4P1T-5](#) [970-003NF20-4P1N-1](#) [970-](#)
[003NF28-4P1N-1](#) [970-003NF32-2P1N-1](#) [970-003NF32-2S1N-1](#) [970-003NF24-5P1N-1](#) [970-003NF24-5P1N-2](#) [970-](#)
[003NF24-5P1N-3](#) [970-003NF36-16S1N-1](#) [970-003ME36-16BN-1](#) [970-003NF28-9P1N-1](#) [970-003ME18-2S2T-1](#)