

TNC Male Right Angle Connector Clamp/Solder Attachment For RG178

LCCN3027



Configuration

- TNC Male Connector
- 50 Ohms
- Right Angle Body Geometry
- RG178 Interface Type
- Clamp/Solder Attachment

Features

- Designed to industry standard interface dimensions
- Quality body materials and plating
- Clamp/solder attachment
- Operates to 3 Ghz

Applications

- RF Boxes and components
- RF Test Systems
- General Purpose RF Interconnect
- Laboratory applications

Description

L-com's TNC male right angle connector for RG178 coax uses a crimp/solder attachment method. This TNC connector is one of the many RF coaxial connectors in L-com's product line up and like all our products, they will ship the same day. Our TNC male right angle connector operates up to a maximum frequency of 3 GHz. The specifications and a basic dimensional drawing for LCCN3027 male TNC right angle connector can be found in this datasheet PDF. L-com's portfolio of RF and microwave connectors allows users to choose from a large number of options when building assemblies to fit their RF interconnect needs. RF cables can be created to fulfill many interconnect applications ranging from In the Box hookup, test equipment connectivity or as part of a system installation. In addition to an offering of RF connectors and coaxial cable, L-com offers both standard and custom cable assemblies to fit a customer's specific needs.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.5:1	
Operating Voltage (AC)			500	Vrms

Mechanical Specifications

Size

Length	1.45 in [36.83 mm]
Width/Dia.	0.59 in [14.99 mm]
Height	1.15 in [29.21 mm]
Weight	0.1 lbs [45.36 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[TNC Male Right Angle Connector Clamp/Solder Attachment For RG178 LCCN3027](#)

TNC Male Right Angle Connector Clamp/Solder Attachment For RG178

LCCN3027



Material Specifications

Description	Material	Plating
Contact	Brass	Gold 30µ in. minimum
Insulation	PTFE	
Body	Brass	Nickel 100µ in. minimum
Coupling Nut	Brass	Nickel 100µ in. minimum

Environmental Specifications

Temperature

Operating Range -65 to +165 °C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:


TNC Male Right Angle Connector Clamp/Solder Attachment For RG178 from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: TNC Male Right Angle Connector Clamp/Solder Attachment For RG178 LCCN3027

URL: <https://www.l-com.com/tnc-male-standard-rg178-connector-lccn3027-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

TNC Male Right Angle Connector Clamp/Solder Attachment For RG178

L-com CAD Drawing



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[CTL3VGAMF-10TZ](#)