



## Cable fixing plate type KAF




### Product information

The cable fixing plate KAF is suitable for simultaneously holding and relieving the strain of cables in the control cabinet. Designed to be mounted on a standard 35 mm top-hat rail (EN 50022; Niedax 2934;2936) or on a C-rail (Niedax 2970;2971). Installation is a simple snap-in process.

- Approved for railway technology (EN 45545-2 / NFPA 130)

### Information, conformities and approvals



Article	Order No.	Color	No. Cables	PU pcs.
KAF 11	87201010	Black	1	1
KAF 75	87201014	Black	5	1
KAF 140	87201018	Black	9	1

Article	Order No.	A mm	B mm	a mm	EH mm	K mm	L mm	M mm
KAF 75	87201014	75	40	63	11	13.5	12	9.3
KAF 140	87201018	139.5	40	127.8	11	13.5	12	9.3

### Material properties



Polyamide 6.6



## Cable fixing plate type KAF

### Thermal properties



Temperature / temperature range

-40 °C – 125 °C

### Fire properties



Fire classification

V0



Fire properties as per EN 45545-2

C.I.T. R22 / R23 HL3 :0,44 EN 17084  
Ds (max.) R22 / R23 HL3 :≥ 32 % ISO 4589-2  
LOI R22 / R23 HL3 :59 ISO 5659-2



Resistant to:

Alcohol  
Greases  
Fuels  
Lyes  
Mineral oils  
Weak acids

### Technical information



LABS free



According to ISO 4892-2

### Assembly method



### Conformity



RoHS (EC Directive 2011/65/EU)

### Approvals and operating permits



EU railway approval



GL approval



## Cable fixing plate type KAF

### Classification

ETIM 9: EC000322  
ECLASS 14: 27400604  
UNSPSC 26.0801: 39121719

### General information



Made in Germany

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murrplastik:](#)

[87201010](#) [87201018](#) [87201014](#)