

**Series 802 “Aqua Mouse”
Crimp Receptacles
802-002**



Series 802
Submersible




How to Order Series 802 Crimp Receptacles

Series 802 Crimp Receptacles are available in two shell styles:

Jam Nut Mount for rear panel mounting.

Box Mount for front mounting to a panel.

How To Order Series 802 Crimp Receptacles

Series	Shell Style	Shell Material / Finish	Shell Size / Insert Arrangement	Contact Type	Shell Key Position
802-002 Crimp Receptacles	07 Jam Nut 	Z1 Stainless Steel, with Passivated Finish	6-4 4 Contacts 	P Pin	N Normal
	02 Square Flange 		6-7 7 Contacts 	S Socket	Alternate Key Positions X Y Z
			9-19 19 Contacts 		

Part Number Example

802-002

—07

Z1


6 — 4

S


N

Series 802 Crimp Receptacle Dimensions

Series 802 Jam Nut Receptacle Dimensions



Series 802 Box Mount Receptacle Dimensions



Series 802 Crimp Receptacle Dimensions

Layout	A	Ø B Max	C Thread	Ø D	E	F
6-4	.500 (12.7)	.906 (23.0)	.5625-20 UN-2A	.30 (7.6)	.875 (22.2)	.625 (15.9)
6-7	.500 (12.7)	.906 (23.0)	.5625-20 UN-2A	.30 (7.6)	.875 (22.2)	.625 (15.9)
9-19	.688 (17.5)	1.062 (27.0)	.750-20 UNEF-2A	.52 (13.2)	1.062 (27.0)	.812 (20.6)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[802-002-02Z16-7PN](#) [802-002-07Z19-19PN](#) [802-002-07Z16-7SN](#) [802-002-07Z16-4PN](#)