

GC2X20MPS12-247

1200V 40A SiC Schottky MPS™ Diode




Silicon Carbide Schottky Diode

| | | |
|-------------------------------------|---|----------|
| V_{RRM} | = | 1200 V |
| I_F ($T_C = 135^\circ\text{C}$) | = | 64 A * |
| Q_C | = | 214 nC * |


Features

- Low V_F for High Temperature Operation
- Enhanced Surge and Avalanche Robustness
- Superior Figure of Merit Q_C/I_F
- Low Thermal Resistance
- Low Reverse Leakage Current
- Temperature Independent Fast Switching
- Positive Temperature Coefficient of V_F
- High dV/dt Ruggedness

Package



T0-247-3



Advantages

- Improved System Efficiency
- High System Reliability
- Optimal Price Performance
- Reduced Cooling Requirements
- Increased System Power Density
- Zero Reverse Recovery Current
- Easy to Parallel without Thermal Runaway
- Enables Extremely Fast Switching

Applications

- Power Factor Correction (PFC)
- Electric Vehicles and Battery Chargers
- Solar Inverters
- High Frequency Converters
- Switched Mode Power Supply (SMPS)
- Motor Drives
- Anti-Parallel / Free-Wheeling Diode
- Induction Heating & Welding

Absolute Maximum Ratings (At $T_C = 25^\circ\text{C}$ Unless Otherwise Stated)

| Parameter | Symbol | Conditions | Values | Unit | Note |
|---|----------------|--|------------|----------------------|--------|
| Repetitive Peak Reverse Voltage (Per Leg) | V_{RRM} | | 1200 | V | |
| Continuous Forward Current (Per Leg / Per Device) | I_F | $T_C = 100^\circ\text{C}, D = 1$ | 46 / 92 | A | Fig. 4 |
| | | $T_C = 135^\circ\text{C}, D = 1$ | 32 / 64 | | |
| | | $T_C = 157^\circ\text{C}, D = 1$ | 20 / 40 | | |
| Non-Repetitive Peak Forward Surge Current, Half Sine Wave (Per Leg) | $I_{F,SM}$ | $T_C = 25^\circ\text{C}, t_P = 10 \text{ ms}$ | 200 | A | |
| | | $T_C = 150^\circ\text{C}, t_P = 10 \text{ ms}$ | 160 | | |
| Repetitive Peak Forward Surge Current, Half Sine Wave (Per Leg) | $I_{F,RM}$ | $T_C = 25^\circ\text{C}, t_P = 10 \text{ ms}$ | 120 | A | |
| | | $T_C = 150^\circ\text{C}, t_P = 10 \text{ ms}$ | 84 | | |
| Non-Repetitive Peak Forward Surge Current (Per Leg) | $I_{F,MAX}$ | $T_C = 25^\circ\text{C}, t_P = 10 \mu\text{s}$ | 1000 | A | |
| i^2t Value (Per Leg) | $\int i^2 dt$ | $T_C = 25^\circ\text{C}, t_P = 10 \text{ ms}$ | 200 | A^2s | |
| Non-Repetitive Avalanche Energy (Per Leg) | E_{AS} | $L = 1.8 \text{ mH}, I_{AS} = 20 \text{ A}$ | 360 | mJ | |
| Diode Ruggedness (Per Leg) | dV/dt | $V_R = 0 \sim 960 \text{ V}$ | 200 | V/ns | |
| Power Dissipation (Per Leg / Per Device) | P_{TOT} | $T_C = 25^\circ\text{C}$ | 312 / 624 | W | Fig. 3 |
| Operating and Storage Temperature | T_j, T_{stg} | | -55 to 175 | $^\circ\text{C}$ | |

* Per Device

GC2X20MPS12-247

1200V 40A SiC Schottky MPS™ Diode




Electrical Characteristics (Per Leg)

| Parameter | Symbol | Conditions | Values | | | Unit | Note |
|-------------------------|--------|---|--------|--|------|---------------|--------|
| | | | Min. | Typ. | Max. | | |
| Diode Forward Voltage | V_F | $I_F = 20\text{ A}, T_j = 25^\circ\text{C}$ $I_F = 20\text{ A}, T_j = 175^\circ\text{C}$ | | 1.5 1.9 | 1.8 | V | Fig. 1 |
| Reverse Current | I_R | $V_R = 1200\text{ V}, T_j = 25^\circ\text{C}$ $V_R = 1200\text{ V}, T_j = 175^\circ\text{C}$ | | 2 22 | 10 | μA | Fig. 2 |
| Total Capacitive Charge | Q_C | $I_F \leq I_{F,\text{MAX}}$ $di_F/dt = 200\text{ A}/\mu\text{s}$ | | 74 107 | | nC | Fig. 7 |
| Switching Time | t_S | | | $V_R = 400\text{ V}$ $V_R = 800\text{ V}$ | < 10 | ns | |
| Total Capacitance | C | $V_R = 1\text{ V}, f = 1\text{ MHz}$ $V_R = 800\text{ V}, f = 1\text{ MHz}$ | | 1218 71 | | pF | Fig. 6 |

Thermal/Package Characteristics


| Parameter | Symbol | Conditions | Values | | | Unit | Note |
|---|------------|--------------------|--------|------|------|---------------------------|--------|
| | | | Min. | Typ. | Max. | | |
| Thermal Resistance, Junction - Case (Per Leg) | R_{thJC} | | | 0.48 | | $^\circ\text{C}/\text{W}$ | Fig. 9 |
| Weight | W_T | | | 6.1 | | g | |
| Mounting Torque | T_M | Screws to Heatsink | | | 1.1 | Nm | |

Figure 1: Typical Forward Characteristics (Per Leg)




$$I_F = f(V_F, T_J); t_P = 250 \mu s$$

Figure 2: Typical Reverse Characteristics (Per Leg)




$$I_R = f(V_R, T_J)$$

Figure 3: Power Derating Curves (Per Leg)




$$P_{TOT} = f(T_C); T_J = 175^\circ C$$

Figure 4: Current Derating Curves (Typical V_F) (Per Leg)




$$I_F = f(T_C); D = t_P/T; T_J \leq 175^\circ C; f_{SW} > 10kHz$$

Figure 5: Current Derating Curves (Maximum V_F) (Per Leg)




$$I_F = f(T_C); D = t_P/T; T_J \leq 175^\circ\text{C}; f_{SW} > 10\text{kHz}$$

Figure 6: Typical Junction Capacitance vs Reverse Voltage Characteristics (Per Leg)




$$C = f(V_R); f = 1\text{MHz}$$

Figure 7: Typical Capacitive Charge vs Reverse Voltage Characteristics (Per Leg)




$$Q_C = f(V_R); f = 1\text{MHz}$$

Figure 8: Typical Capacitive Energy vs Reverse Voltage Characteristics (Per Leg)




$$E_C = f(V_R); f = 1\text{MHz}$$

Figure 9: Transient Thermal Impedance (Per Leg)



$$Z_{th,jc} = f(t_p, D); D = t_p / T$$

Figure 10: Forward Curve Model (Per Leg)



$$I_F = f(V_F, T_j)$$

Forward Curve Model Equation:

$$I_F = (V_F - V_{BI}) / R_{DIFF} \text{ (A)}$$

Built-In Voltage (V_{BI}):

$$V_{BI}(T_j) = m \times T_j + n \text{ (V)}$$

$$m = -0.00123 \text{ (V/°C)}$$

$$n = 0.995 \text{ (V)}$$

Differential Resistance (R_{DIFF}):

$$R_{DIFF}(T_j) = a \times T_j^2 + b \times T_j + c \text{ (}\Omega\text{)}$$

$$a = 5.96e-07 \text{ (}\Omega/\text{°C}^2\text{)}$$

$$b = 8.46e-05 \text{ (}\Omega/\text{°C}\text{)}$$

$$c = 0.0251 \text{ (}\Omega\text{)}$$

Forward Power Loss Equation:

$$P_{LOSS} = V_{BI}(T_j) \times I_{AVG} + R_{DIFF}(T_j) \times I_{RMS}^2$$


GC2X20MPS12-247

1200V 40A SiC Schottky MPS™ Diode




Package Dimensions


TO-247-3 Package Outline



Recommended Solder Pad Layout



Package View



NOTE

1. CONTROLLED DEIMENSION IS INCH. DIMENSION IN BRACKET IS MILLIMETER.
2. DIMENSIONS DO NOT INCLUDE END FLASH, MOLD FLASH, MATERIAL PROTRUSIONS.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS 2), as adopted by EU member states on January 2, 2013 and amended on March 31, 2015 by EU Directive 2015/863. RoHS Declarations for this product can be obtained from your GeneSiC representative.

REACH Compliance

REACH substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact a GeneSiC representative to insure you get the most up-to-date REACH SVHC Declaration. REACH banned substance information (REACH Article 67) is also available upon request.

This product has not been designed or tested for use in, and is not intended for use in, applications implanted into the human body nor in applications in which failure of the product could lead to death, personal injury or property damage, including but not limited to equipment used in the operation of nuclear facilities, life-support machines, cardiac defibrillators or similar emergency medical equipment, aircraft navigation or communication or control systems, or air traffic control systems.

GeneSiC disclaims all and any warranty and liability arising out of use or application of any product. No license, express or implied to any intellectual property rights is granted by this document.

Related Links

- SPICE Models: https://www.genesicsemi.com/sic-schottky-mps/GC2X20MPS12-247/GC2X20MPS12-247_SPICE.zip
- PLECS Models: https://www.genesicsemi.com/sic-schottky-mps/GC2X20MPS12-247/GC2X20MPS12-247_PLECS.zip
- CAD Models: https://www.genesicsemi.com/sic-schottky-mps/GC2X20MPS12-247/GC2X20MPS12-247_3D.zip
- Evaluation Boards: <https://www.genesicsemi.com/technical-support>
- Reliability: <https://www.genesicsemi.com/reliability>
- Compliance: <https://www.genesicsemi.com/compliance>
- Quality Manual: <https://www.genesicsemi.com/quality>

www.genesicsemi.com/sic-schottky-mps/



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[GeneSiC Semiconductor:](#)

[GC2X20MPS12-247](#)