

Sound Level Meter, Class 2

GNV-100



Features:

- Meets IEC 61672-1 Class 2 requirements
- Fast and slow time weighting
- 60 dB dynamic range
- A and C frequency weighting
- AC and DC outputs available from standard 3.5 mm coaxial socket for use with a frequency analyzer, level recorder, FFT analyzer, etc.
- Min/max function
- Battery capacity indicator
- Analog bar graph and digital display
- Tripod mount for long term monitoring (tripod not included)
- Includes windscreen, 9 V battery and hard carrying case

Applications:

- OSHA compliance
- Noise ordinance checks
- General purpose noise surveys
- Commercial construction
- R&D labs
- Education

Description:

The Global Specialties GNV-100 Sound Level Meter is a portable sound level meter used to capture the dB level of one's surrounding environment. The meter meets the IEC Class 2 requirements, which makes it ideal for sound hazard measurements. The hand held design also comes with a tripod mount for the option of hands free use (tripod not included). Fast time sampling of one measurement every 125 ms combined with the wide dynamic range of 60 dB provides high detail output from the crisp LCD display.



Specifications:

Safety Standard Applied	IEC 61672-1 Class 2
Included Accessories	One 9 V battery, instruction manual, windscreen, carrying case
Operating Limits and Functions	
Measuring Level Ranges	Low: 30 to 90 dB
	Med: 50 to 110 dB
	High: 70 to 130 dB
Sample Rate	Fast 125 ms
	Slow 1000 ms
Accuracy	± 1.4 dB @ 94 dB, 1 kHz
Dynamic Range	60 dB
Frequency Range	20 Hz to 8 kHz
Frequency Weighting	A / C
Microphone	1/2 Inch electret condenser
Displays	
Digital Display	4 Digit display
	Resolution: 0.1 dB
	Display Update: 0.5 sec
Analog Display	30 Segment bar graph
	Resolution: 2 dB
	Display Update: 100 ms
Alarm Functions	OVER and UNDER alarm functions indicating when sound level is outside the set range
Electrical Specifications	
AC Output	1 Vrms at full scale
DC Output	10 mV/dB
Power Supply	One 9 V battery: 006P, 6F22, NEDA 1604
Battery Life	Approx. 50 hours
Environmental Specifications	
Operating Temperature	0 to 40 °C (32 to 104 °F)
Operating Humidity	10 to 90% Relative humidity
Storage Temperature	-10 to 60 °C (14 to 140 °F)
Storage Humidity	10 to 75% Relative humidity
Altitude	Up to elev. of 2000 meters (~6,500 ft.)
Mechanical Specifications	
Dimensions	258 x 55 x 25 mm (10.2 x 2.2 x 1.0")
Weight	Approx. 185g (6.5 oz.)

Contact Info:

Toll Free: 800-572-1028 (US Only)
Phone: 714-221-9330
Fax: 714-921-9849
22820 Savi Ranch Parkway
Yorba Linda, CA 92887-4610 USA
www.globalspecialties.com

Specifications and appearance subject to change without notice
DGNV10000 052919

2 - www.globalspecialties.com



Copyright © 2019, Cal Test Electronics, Inc.
All rights reserved. Information in this publication supersedes that in all previously published material. Trade names referenced are the service marks, trademarks or registered trademarks of their respective companies.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Global Specialties:](#)

[GNV-100](#)