


### Mini Temperature/Humidity Meter



#### Description:

The M120 uses a highly accurate sensor chip to measure relative humidity and temperature. It is perfect for many industrial applications, laboratory and other types of work environments. Durable, reliable, and easy to use, the M120 features:

Features:

- Dual display of temperature and humidity
- °C / °F modes
- Simultaneously hold both temperature and humidity readings
- Simultaneously hold both maximum and minimum and average readings (MAX/MIN/AVG)
- Auto-power off
- Low Battery Indicator 
- DEW-POINT and WET-BULB temperature measurement

#### Applications:

- Measure the temperature and humidity both indoors and out in the field



WARRANTY



### Technical Specifications


<b>Display</b>	Dual LCD display. The maximum value on the primary display is 999. The maximum value on secondary display is 999.
<b>Sampling Rate</b>	1 sample per second
<b>Measuring Range</b>	-20.0°C ~ +50.0°C (-4.0°F - +122.0°F) 1.0% ~ 99 %RH
<b>Accuracy</b>	Humidity : ±3.5% for 20~90% ± 5% for 1~19.9 and 90.1~99 Temperature : ± 1.0°C, ±1.8°F
<b>Power Supply</b>	2 batteries 1.5V AAA
<b>Battery life</b>	50 hours during consecutive use
<b>Operating Conditions</b>	0°C ~ +60°C, <95% RH. (non-condensing)
<b>Storage Conditions</b>	-10 to 60°C, <70% RH. (non-condensing)
<b>Dimensions</b>	107 × 48 × 23 mm (H × W × D)
<b>Weight</b>	80g (excluding the battery)
<b>Warranty</b>	Limited two-year warranty

### Includes:

- Meter
- User Manual
- Carrying Case
- 2x 1.5V AAA Batteries

### This instrument conforms to:

- EN61326-1 (2006)
- CE
- Directives:  
89/336/EEC  
(Electromagnetic Compatibility) and  
73/23/EEC (Low Voltage) as amended  
by 93/68/EEC (CE Marking).



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Global Specialties:](#)

[M120](#)