


PB-104M

3220 TIE-POINT, EXTERNALLY POWERED SOLDERLESS BREADBOARD

Applications

The PB-104M Externally Powered Solderless Breadboard is a great way to prototype low frequency or DC powered circuits. It is ideal for:

- Educational labs
- Hobbyists



Features

- Comes fully assembled
- Externally powered
- 3220 Tie-points
- 4 Binding posts
- 19 mm standard spaced binding posts
- ABS plastic body
- Square hole style
- Nickel plated phosphor bronze spring clip contacts
- Aluminum back plate
- Rubber feet
- Fits 0.4-0.7 mm wire diameter
- Fits 28 total 16-pin ICs
- Measures 21 x 24 x 2.7 cm
- Weighs 600 g
- Maximum current capacity of 1.5 A at 36 V
- RoHS compliant
- Three-year warranty

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Global Specialties:](#)

[PB-104M](#)