

**GREENLEE®**

A Textron Company

TG-1000 Infrared Thermometer

TG-2000 Dual Laser Infrared Thermometer

**Contact and non-contact
temperature measurement**



SAFE, QUICK, CONVENIENT TEMPERATURE READINGS.

Infrared thermometers provide speed, convenience, accessibility and safety when taking temperature measurements. The new TG-1000 and TG-2000 both feature the high optical performance, measurement accuracy and quality necessary for the professional. Both IR thermometers include the capability to display temperature in either Fahrenheit or Celsius, vivid backlight displays, digitally adjustable emissivity, adjustable high-low temperature alarms, plus minimum, maximum, difference and average functions. The Type-K thermocouple input on the TG-2000 provides the accuracy needed for critical measurements of metallic objects, internal temperatures and ambient temperatures, with the flexibility of choosing probe styles for the task at hand.

Why Use IR Thermometers in my Application?

Temperature is often the first indication of a developing problem and IR thermometers can be used as a screening technique for situations that may require further analysis with other Greenlee tools such as a digital multimeter or clamp meter. A non-contact IR thermometer allows you to stay a safe distance from the object and get the most accurate readings across a wide range of temperatures.

Where Can IR Thermometers be Used?

Some environments where IR thermometers are used include: Industrial, HVAC/R, Electrical, Utility and MRO/Facility Maintenance.

Features

Both TG-1000 and TG-2000 offer:

- Safe, non-contact temperature measurement.
- Laser spot indicator shows approximate center of target measurement area.
- Display temperatures in either Fahrenheit or Celsius.
- Adjustable emissivity for optimum temperature reading accuracy on a wide range of materials and surfaces.
- Min, Max, Difference and Average temperature functions.
- Backlight display for easy readings in any environment.
- Auto power off for longer battery life.


Specifications

FEATURE	TG-1000	TG-2000
Range - F:	-76 ~ 1022	-76 ~ 1157
Range - C:	-60 ~ 550	-60 ~ 625
D:S Ratio:	12:1	16:1
Laser:	•	Dual
K-type Contact:		•
Emissivity:	.10 ~ 1.00	.10 ~ 1.00
Backlight:	•	•
Form Factor:	Gun	Gun
Max:	•	•
Min:	•	•
Difference:	•	•
Average:	•	•
Alarms:	Hi/Low	Hi/Low

Ordering Information

CAT NO.	UPC NO.	DESCRIPTION	QTY.
TG-1000	783310001034	Infrared Thermometer	1
TG-2000	783310001041	Dual Laser Infrared Thermometer	1

DISTRIBUTOR INFORMATION:



GREENLEE®
A Textron Company

www.greenlee.com • MA-5655 07/11
4455 Boeing Drive • Rockford, IL 61109-2988 • USA • 815-397-7070
©2011 Greenlee Textron Inc. • An ISO 9001 Company • Printed in USA
Greenlee Textron Inc. is a subsidiary of Textron Inc.

USA
Tel: 800.435.0786
Fax: 800.451.2632

CANADA
Tel: 866.384.8813
Fax: 800.524.2653

INTERNATIONAL
Tel: +1.815.397.7070
Fax: +1.815.397.9247

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Greenlee:](#)

[TG-1000](#) [TG-2000](#)