



ADAPTER, SOC, LC

Fiber Optic Instrument Adapters SOC

Cat No: T10LC

UPC No: 783310606000

Description

- SOC adapters provide direct connectivity for Tempo FiberTOOLS to a wide range of industry-standard fiber optic connectors
- Adapter design ensures maximum accuracy and repeatability when performing critical measurements on fiber optic systems
- Easy to clean and use
- Single-mode and multimode compatible
- SOC adapters are compatible with both PC and Angled APC physical contact interfaces
- SOC (Snap-On Connector) adapter is used on all power meters and 250 "B" series LED Sources

Specifications

- Application : Used on all power meters and 250 "B" series LED Sources
- Fiber Type : LC
- Type : Snap On Connector

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Greenlee:

[PA1561](#) [04598](#) [29529](#) [30225](#) [30227](#) [3037AV](#) [00626](#) [20988](#) [31849](#) [35168](#) [7310SB](#) [KA12-2](#) [12357](#) [7212SP-1D](#)
[MSS100](#) [04608](#) [19193](#) [21115](#) [24462](#) [2983AV](#) [35158](#) [35160](#) [7904ESB](#) [PA1363](#) [7212SP-1-1/4D](#) [00630](#) [SP-](#)
[LOCK](#) [00627](#) [00629](#) [MINI-CFO](#) [0163-0001-1](#) [04599](#) [657](#) [730PBB-3-3/4](#) [737BB](#) [77P-1-1/4P](#) [06302](#) [12356](#)
[7804ESB](#) [12341](#) [PA8022](#) [KK50LFLEX](#) [34758](#) [54170](#) [31124](#) [35202](#) [45039](#) [45040](#) [7309E](#) [77P-2P](#) [12347](#) [04607](#)
[04609](#) [1433AVBB](#) [23955](#) [2984AV](#) [7646PG-SB](#) [1430AV](#) [21316](#) [25094](#) [0159-13](#) [12338](#) [28161](#) [2981AV](#) [3208AV](#)
[35162](#) [35178](#) [730MBB](#) [0254-50](#) [7212SP-1-1/4P](#) [7212SP12](#) [00622](#) [00624](#) [1926AA](#) [7360SB](#) [77P-1-1/2P](#) [20495](#)
[04605](#) [04602](#) [KA12-3/0](#) [31133](#) [32012](#) [33786](#) [35169](#) [7304](#) [7306](#) [7212SP11](#) [17687](#) [28159](#) [31122](#) [31128](#) [31131](#)
[KA12-4](#) [52177](#) [52178](#) [DM-45](#) [LS50LB](#) [00625](#) [7361SB](#) [738BB](#)