




Quality Products. Service Excellence.

Studio Grade Impedance Matching Transformers 1140 Series

Features



- Designed with Nickel alloy cores for high performance and Wide Bandwidth
- Frequency Response: 20 Hz – 20 kHz ± 0.35 dB, (ref. @ 1 kHz)
- Low distortion at levels up to +27 dBu @ 20 Hz.
- Excellent Shielding – Mu Metal enclosures
- Line Output Transformers are open style (not Mu Metal)



Microphone Input Transformers

Part No.	Impedance Ratio	Turns Ratio	Max Input @ 20Hz	THD @ 20Hz	Frequency Response 20Hz / 20kHz
1140-MN-A	150:15K	1:10	-2.5 dBu	0.02%	-0.05 dB/ -0.06 dB
1140-MN-B	150: 3.8K	1:5	+7.0dBu	0.015%	-0.04 dB/ +0.00 dB

Microphone Splitter Transformers

Part No.	Impedance Ratio	Turns Ratio	Max Input @ 20Hz	THD @ 20Hz	Frequency Response 20Hz / 20kHz
1140-MS-A	150:150	1:1	+2.0 dBu	0.05%	-0.14 dB/-0.06 dB
1140-MS-B	150:150:150	1:1	+2.0 dBu	0.030%	-0.08 dB/+0.06 dB
1140-MS-C	150:150:150:150	1:1:1:1	+11 dBu	0.030%	-0.05 dB/+0.20 dB

Line Input Transformers

Part No.	Impedance Ratio	Turns Ratio	Max Input @ 20Hz	THD @ 20Hz	Frequency Response 20Hz / 20kHz
1140-LN-A	10k:20k	1:1.414	+16 dBu	0.02%	-0.04 dB/+0.10 dB
1140-LN-B	10K:10K	1:1	+20 dBu	0.020%	-0.03 dB/+0.10 dB
1140-LN-C	36K:2.2K / 10K:600	4:1	+26 dBu	0.015%	-0.20 dB/+0.05 dB
1140-LN-D	40K:2.4K	4:1	+21 dBu	0.060%	-0.12 dB/+0.06 dB
1140-LN-E	600:600	1:1	+19 dBu	0.020%	-0.06 dB/+0.00 dB

Line Output Transformers

Part No.	Impedance Ratio	Turns Ratio	Max Input @ 20Hz	THD @ 20Hz	Frequency Response 20Hz / 20kHz
1140-LU-A	10K:600	4:1	+23 dBu	0.00%	-0.06 dB/+0.04 dB
1140-LU-B	600:600	1:1	+21 dBu	0.150%	-0.20 dB/+0.03 dB
1140-LU-C	600:600	1:1	+18 dBu	0.001%	-0.05 dB/+0.02 dB
1140-LU-D	600:600	1:1	+24 dBu	0.080%	-0.18 dB/+0.03 dB
1140-LU-E	600:600	1:1	+22 dBu	0.001%	-0.03 dB/+0.02 dB
1140-LU-F	600:150	2:1	+27 dBu	0.001%	-0.01 dB/+0.01 dB
1140-LU-G	600:600	1:1	+27 dBu	0.001%	-0.02 dB/+0.02 dB

open style (not Mu Metal)

Direct Box Transformers

Part No.	Impedance Ratio	Turns Ratio	Max Input @ 20Hz	THD @ 20Hz	Frequency Response 20Hz / 20kHz
1140-DB-A	200K:1.5K	12:1	+22 dBu	0.02%	-0.07 dB/-0.07 dB

Tags: audio transformer, studio grade, mu metal, nickel core, distortion, shielding, output, input, microphone, splitter, line, direct box

Data subject to change without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[1140-LN-E](#) [1140-LN-B](#) [1140-LU-C](#) [1140-LU-F](#) [1140-MS-C](#) [1140-DB-A](#) [1140-LN-C](#) [1140-LU-D](#) [1140-LU-G](#) [1140-LU-A](#) [1140-LN-A](#) [1140-LU-B](#) [1140-LN-D](#) [1140-MS-B](#) [1140-LU-E](#) [1140-MN-A](#) [1140-MN-B](#) [1140-MS-A](#)