


HiPer 55116 Radio Mount Audio Receptacle with PC tails and 3 ground pins 152-012



**TACTICAL
INTERCONNECT
SOLUTIONS**

RADIO MOUNT JAM NUT RECEPTACLE WITH NON-RIGID SPRING CONTACTS, PC TAIL, WITH 3 GROUND PINS

MATES WITH 152-001 AND 152-002, 151-001 AND 151-002, AND STANDARD MIL-DTL-55116 PLUGS



How To Order			
Sample Part Number	152-012	-2	-4
Product Series	HiPer 55116 radio-mount jam nut receptacle with PC tail contacts and 3 ground pins		
Connector Style	-1 = U-183 type 5-pin -2 = U-183 type 6-pin		
PC tail type	see Table II		










Table II: PC Tail Dimensions

Dash No.	Ø A	Ø B	C	D
-1	.040	.089	.115	.169
-2	.040	—	—	.437
-3	.028	.089	.188	.590
-4	.028	.089	.125	.194
-5	.028	.089	.208	.257
-6	.040	—	—	.110
-7	.028	.089	.150	.437
-8	.030	—	—	.120
-9	.028	.089	.140	.390
-10	.040	—	—	.744
-11	.030	—	—	.564
-12	.040	—	—	.110
-13	.040	—	—	.900
-14	.040	—	—	.257

MATERIALS AND FINISHES

Shell and nut: Stainless steel/PTFE-nickel plated (matte finish)
Inserts: Diallylphthalate resin type SDG-F
Seals: Ethylene propylene rubber
Contacts: Copper alloy/gold plate
Contact spring: CRES/passivated

NOTES

Connectors are identified with Glenair's name, part number and date code.
Meets interface configurations and IAW specifications of MIL-DTL-55116 Type C, and exceeds the following:
Shell-to-shell conductivity: 2.5 milliohms max.
Cable shield-to-shell conductivity: 2.5 milliohms max.
Contact resistance (mated): 15 milliohms max. average; 20 milliohms max.
Pressure sealing (mated & un-mated): IP68 (10 meters of standing water / 1 hr.)
Salt atmosphere: 1,000 hours (MIL-STD-202, Method 101E)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

152-012-2-14