




Quality Products. Service Excellence.

Heavy Duty Outlet Strip 1581 Series

10A | 100-240V | C13 Outlets

Features



- Rated 100-240VAC (TUV), 120-240VAC (UL), 10 A, 50/60 Hz and designed for use with IEC power cords.
- All-metal housing. Case is made of tough extruded aluminum with a black powder-coated steel cover.
- Available with either rocker type on/off switch with green light or a green pilot light to indicate power on.
- Mounting feet with keyhole slots allow temporary work station mounting if desired.

Specifications

- One IEC 320 - C14 inlet, and 4, 5, 6 or 8 IEC 320 - C13 outlets.
- Includes 10A circuit breaker to prevent accidental line overload.
- cULus Listed UL 62368-1 (2nd Edition), 2014-12-01, and CAN/CSA C22.2 No. 62368-1-14 (2nd Edition)
- TÜV-SUD Certified to EN 62368-1:2020/A11:2020, and IEC 62368-1:2018.
- TÜV-SUD tested for EMC Compliance to EN 55032:2015+A11:2020 (CISPR 32:2015+A1:2019) & EN 55035:2017+A11:2020 (CISPR 35:2016).
- CE compliant to the European Low Voltage Directive 2014/35/EU.
- CE compliant to the European EMC Directive 2014/30/EU.
- UKCA compliant to British Electrical Equipment (Safety) Regulations 2016 (S.I. 2016/1101).
- UKCA compliant to British Electromagnetic Compatibility Regulations 2016 (S.I. 2016/1091).
- TAA compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.



Accessories

- Rack Cabinet Vertical Mount Adaptor
- Power Cords

Illuminated On/Off Switch Part No.	Illuminated Light Only Part No.	Overall Dimensions			Outlet Qty	Outlet Type	Inlet Type
		Height	Width	Length			
1581H4	1581T4	2.33	2.13	10.18	4	C13	C14
1581H5	1581T5	2.33	2.13	11.75	5	C13	C14
1581H6	1581T6	2.33	2.13	13.36	6	C13	C14
1581H8	1581T8	2.33	2.13	16.51	8	C13	C14

Replacement Mounting Foot (One Foot)

Part No.	1584MF
----------	--------

Tags: IEC

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[1581T6](#) [1581T4](#) [1581T5](#) [1581T8](#) [1581H8](#) [1581H5](#) [1581H6](#) [1581H4](#)