

CONNECTOR DESIGNATORS A-F-H-L-S ROTATABLE COUPLING

Product Series — 370 F S 001 M 16 10 M 6

Connector Designator —

Angle and Profile —
A = 90°
B = 45°
S = Straight

Basic Part No. —


Length: S only
(1/2 inch increments:
e.g. 6 = 3 inches)

Strain Relief Style
(H, A, M, D)


Cable Entry (Tables X, XI)

Shell Size (Table I)




Finish (Table II)




STYLE 2
(STRAIGHT
See Note 1)




STYLE 2
(45° & 90°
See Note 1)




STYLE H
Heavy Duty
(Table X)




STYLE A
Medium Duty
(Table XI)



STYLE M
Medium Duty
(Table XI)



STYLE D
Medium Duty
(Table XI)



370-001

Submersible Cable Sealing Backshell

with Strain Relief

Low Profile - Rotatable Coupling



37

TABLE III: ELBOW DIMENSIONS

Shell Size		E		F		G		H	
Conn. Desig.	H	Max		Max		Max		Max	
A-F-L-S									
08	09	.457	(11.6)	1.810	(46.0)	.500	(12.7)	1.820	(46.2)
10	11	.520	(13.2)	1.869	(47.5)	.595	(15.1)	1.940	(49.3)
12	13	.582	(14.8)	1.929	(49.0)	.610	(15.5)	1.960	(49.8)
14	15	.645	(16.4)	2.359	(59.9)	.700	(17.8)	2.369	(60.2)
16	17	.738	(18.7)	2.469	(62.7)	.885	(22.5)	2.459	(62.5)
18	19	.926	(23.5)	2.659	(67.5)	.975	(24.8)	2.629	(66.8)
20	21	.926	(23.5)	2.659	(67.5)	.975	(24.8)	2.629	(66.8)
22	23	1.020	(25.9)	2.872	(72.9)	1.125	(28.6)	2.802	(71.2)
24	25	1.020	(25.9)	2.872	(72.9)	1.125	(28.6)	2.802	(71.2)
28		1.145	(29.1)	2.905	(73.8)	1.225	(31.1)	2.955	(75.1)
32		1.207	(30.7)	3.005	(76.3)	1.575	(40.0)	3.205	(81.4)
36		1.238	(31.4)	3.315	(84.2)	1.775	(45.1)	3.255	(82.7)

1. When maximum cable entry (page 21) is exceeded, Style 2 will be supplied. Dimensions E, F, G and H will not apply. Please consult factory.
2. Metric dimensions (mm) are indicated in parentheses.
3. Cable range is defined as the accommodations range for the wire bundle or cable. Dimensions shown are not intended for inspection criteria.
4. Interface O-Ring not supplied with connector designator A.
5. Consult factory for shorter lengths on straight backshells.

TABLE X: CABLE ENTRY

Dash No.	T Max	V Max	Cable Range	
			Min	Max
04	.780 (19.8)	.957 (24.3)	.125 (3.2)	.312 (7.9)
06	.780 (19.8)	1.145 (29.1)	.250 (6.4)	.437 (11.1)
08	.780 (19.8)	1.332 (33.8)	.387 (9.8)	.562 (14.3)
10	.780 (19.8)	1.332 (33.8)	.350 (8.9)	.625 (15.9)
12	.811 (20.6)	1.551 (39.4)	.500 (12.7)	.750 (19.1)
16	.905 (23.0)	1.770 (45.0)	.625 (15.9)	.937 (23.8)
20	1.092 (27.7)	2.113 (53.7)	.875 (22.2)	1.250 (31.8)
24	1.124 (28.5)	2.363 (60.0)	1.000 (25.4)	1.375 (34.9)
28	1.399 (35.5)	2.770 (70.4)	1.250 (31.8)	1.625 (41.3)
32	1.399 (35.5)	3.020 (76.7)	1.437 (36.5)	1.875 (47.6)

See inside back cover fold-out or pages 13 and 14 for unabridged Tables I and II.

TABLE II: STANDARD FINISHES

GLENAIR	
SYMBOL	FINISH
B	Cadmium Plate, Olive Drab
C	Anodize, Black
G	Hard Coat, Anodic
M	Electroless Nickel
NF	Cadmium Plate, Olive Drab Over Electroless Nickel
See Inside Back Cover for Additional Finish Options	

TABLE XI: CABLE ENTRY

Dash No.	W Max	X Max	Y Max	Z Max	Cable Range	
					Min	Max
03*	.437 (11.1)	.760 (19.3)	.843 (21.4)	.630 (16.0)	.156 (4.0)	.250 (6.4)
04*	.437 (11.1)	.760 (19.3)	.906 (23.0)	.755 (19.2)	.188 (4.8)	.312 (7.9)
06*	.500 (12.7)	.760 (19.3)	1.093 (27.8)	.942 (23.9)	.281 (7.1)	.438 (11.1)
08	.563 (14.3)	.760 (19.3)	1.187 (30.1)	1.067 (27.1)	.387 (9.8)	.562 (14.3)
10	.563 (14.3)	.760 (19.3)	1.281 (32.5)	1.192 (30.3)	.375 (9.5)	.625 (15.9)
12	.563 (14.3)	.760 (19.3)	1.500 (38.1)	1.380 (35.1)	.438 (11.1)	.750 (19.1)
16	.656 (16.7)	1.073 (27.3)	1.719 (43.7)	1.535 (39.0)	.625 (15.9)	.938 (23.8)
20	.656 (16.7)	1.323 (33.6)	2.062 (52.4)	1.848 (46.9)	.875 (22.2)	1.250 (31.8)
24	.656 (16.7)	1.323 (33.6)	2.312 (58.7)	2.255 (57.3)	1.000 (25.4)	1.375 (34.9)
28	1.188 (30.2)	1.572 (39.9)	2.719 (69.1)	2.505 (63.6)	1.250 (31.8)	1.625 (41.3)
32*	1.187 (30.1)	1.572 (39.9)	2.969 (75.4)	2.755 (70.0)	1.437 (36.5)	1.875 (47.6)
40*	1.125 (28.6)	1.572 (39.9)	3.531 (89.7)	3.255 (82.7)	1.875 (47.6)	2.375 (60.3)

* Not available in Style M clamp.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[370FS001B0806A3](#) [370FS001B1406H6](#) [370FS001G1412A3](#) [370FS001N1004A3](#) [370FS001N1610H4](#)
[370FS001N1616H4](#) [370FS001N2006A3](#) [370FS001NF1412M5](#) [370FS001NF1616M5](#) [370FS001NF2020M5](#)
[370FS001T1404A4](#) [370HA001N1710H](#) [370HA001NF1504A](#) [370HA001NF1908H](#) [370HA001NF1912H](#)
[370HA001NF2116H](#) [370HA001NF2510H](#) [370HB001NF1506H](#) [370HB001NF2124M](#) [370HS001G2512A3](#)
[370HS001LF1104A3](#) [370HS001M1104A3](#) [370HS001M1506A3](#) [370HS001N1106H3](#) [370HS001N1704A3](#)
[370HS001NF0903A3](#) [370HS001NF1108H4](#) [370HS001NF1312H3](#) [370HS001NF1316H4](#) [370HS001NF1512H4](#)
[370HS001NF1516M4](#) [370HS001NF1710M6](#) [370HS001NF2116H3](#) [370HS001NF2116M6](#) [370HS001NF2510M6](#)
[370HS001NF2516A6](#) [370HS001B2510H6](#) [370AS001NF1412A4](#) [370AS001NF1606A3](#) [370AS001NF2212H3](#)
[370AS001Z11404H2](#) [370HA001M1708A](#) [370HS001M0904A3](#) [370HS001M1706A3](#) [370HS001M1706A4](#)
[370AA001G0804A](#) [370AS001B1608A6](#) [370AS001B2810A6](#) [370AS001B3204A6](#) [370AS001M1204A4](#)
[370AS001M1808M4](#) [370AS001M2004H3](#) [370AS001NF1416M6](#) [370AS001NF2004H3](#) [370FS001G2420A3](#)
[370FS001M1204A3](#) [370FS001N2012H4](#) [370FS001NF2410H3](#) [370HS001B1716H8](#) [370HS001B2316H8](#)
[370HS001G0906A3](#) [370HS001NF1306H3](#) [370AA001B1604A](#) [370AA001B1608A](#) [370AA001B2006A](#)
[370AA001N1212H](#) [370AA001N2224H](#) [370AA001NF1206H](#) [370AA001NF1606A](#) [370AA001NF3220H](#)
[370AB001N2424H](#) [370AS001B1008M4](#) [370AS001M1612H6](#) [370AS001M1810M4](#) [370AS001N1606D3](#)
[370AS001NF1004A3](#) [370AS001NF1006A3](#) [370AS001NF1006A4](#) [370AS001NF1406A3](#) [370AS001NF1408D6](#)
[370AS001NF1412A6](#) [370AS001NF1604H4](#) [370AS001NF1610H3](#) [370AS001NF2416H4](#) [370AS001NF2420H6](#)
[370AA001NF1003A](#) [370AA001NF2428H](#) [370AS001B1404H3](#) [370AS001B1804A6](#) [370AS001B2206H3](#)
[370AS001B2412A6](#) [370AS001B2806A6](#) [370AS001B3620A6](#) [370AS001NF0804H3](#) [370AS001NF2016H4](#)
[370AS001NF2428H8](#) [370FS001B2408H6](#) [370FS001G0804A3](#) [370HA001G2312A](#) [370HS001B1103A3](#)