

5

4

3


2

1





## SPECIFICATION

|                       |           |
|-----------------------|-----------|
| Mating Cycles         | 500       |
| filter type           | C         |
| Capacitance           | 470pF±20% |
| Working Voltage       | 100V      |
| Current Rating        | 7.5A      |
| Insulation Resistance | >1GΩ      |


| FREQUENCY<br>(MHz) | ATTENUATION<br>dB |
|--------------------|-------------------|
| 5                  | -                 |
| 10                 | 1dB               |
| 50                 | 10dB              |
| 100                | 15dB              |
| 500                | 35dB              |
| 1000               | 32dB              |



PCB Layout, Component side



|       |          |      |         |          |      |
|-------|----------|------|---------|----------|------|
|       |          |      |         | Dat.     | Name |
|       |          |      | Detail. | 8-JUL-02 | CV   |
|       |          |      | Insp.   |          |      |
|       |          |      | Stand.  |          |      |
| 33267 | 17/11/05 | JMDR |         |          |      |
| 31058 | 8-JUL-02 | CV   |         |          |      |
| Mod.  | Dat.     | Name |         |          |      |

HARTING EURL  
F-95972 ParisAll Dim. in mm  
Orig. Size DIN A 4D-Sub, male, straight,  
15 Poles, solder pins,  
tin plated shell with  
dimples and holes

TB 09642227220

Sub.

Mo?Mstab/  
Scale

1.5:1

Blatt/ Page

1 / 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09642227220