



Connector Location A

Connector Location B



Mating face acc. to IEC 61076-2-109

M12 X-coded Slim Design,
crimp male straight 8-pole



6.0 to 100	±1%
0.6 to 5.9	+0.04
0.2 to 0.5	+0.02
a [m]	Tolerance [m]


length in 1m step	100	XXX=000
	99	XXX=990
	.	.
	.	.
	12	XXX=120
length in 0.1m step	11	XXX=110
	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	.	.
	0.5	XXX=005
	0.4	XXX=004
Step	0.3	XXX=003
	0.2	XXX=002
XXX		

Part no.	213301018XXXXX
----------	----------------

Type of cable	Temp.	XX
RJI Ethernet stranded cable, 4x2xAWG26/7, Cat.6A, PUR, yellow	-40°C ... +80°C	XX=10
RJI Ethernet flexible cable, 4x2xAWG 26/7, Cat.7A, PUR yellow	-40°C ... +70°C	XX=50
RJI EtherRail cable 4x2xAWG 24/7, Cat.7, PE, black	-40°C ... +80°C	XX=53

All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
	All rights reserved	Created by COSTEA	Inspected by MUNTEANV	Standardisation AVRAM	Date 2017-09-20	State Final Release	
	Department HCS - RO	Title M12 X-coded Cable Assembly				Doc-Key / ECM-Nr. 100542214/UGD/004/D 500000125542	
HARTING Customised Solutions D-32427 Minden		Type TB	Number 213301018XXXXX			Rev. D	Page 1/1

- Protection level: IP65/67



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21330101850005](#) [21330101850010](#) [21330101850020](#) [21330101850100](#) [21330101850050](#) [21330101850040](#)
[21330101850025](#) [21330101850015](#) [21330101850030](#) [21330101850150](#) [21330101850200](#)