



WIRING INFORMATION

J1	Wire color	J2
2-e	Rose	2-e
1-e	Orange	1-e
2-d	Yellow	2-d
1-d	Rose	1-d
2-c	Rose	2-c
1-c	Brown	1-c
2-b	Black	2-b
1-b	Rose	1-b
2-a	Rose	2-a
1-a	Red	1-a
Shell	Braid	Shell

12

e

d

c

b

a

33 27 243 700 0019	7 m
33 27 242 120 0055	12 m
33 27 243 350 0029	3.5 m
33 27 243 400 0028	4 m
33 27 243 300 0027	3 m
33 27 243 060 0026	0.6 m
33 27 242 100 0021	10 m
33 27 243 800 0020	8 m
33 27 243 650 0019	6.5 m
33 27 243 200 0003	2 m
33 27 243 100 0002	1 m
33 27 243 050 0001	0.5 m
Dim. L	

NOTES /

- CABLE ASSEMBLY IS MANUFACTURED PER RELEVANT JOB.
- MECHANICAL REQUIREMENTS
 - OPERATING TEMPERATURE = -20° TO +105°C
 - MATING CYCLES : 250, PERFORMANCE LEVEL 2 (IEC 60512-5)
- THE CONNECTOR COMPLIES REQUIREMENT : IEC 61076-4-107
- WHITE LABEL INFORMATION:

DATE CODE

HARTING P/N

- CABLE MUST BE PERFORMED HI-POT TEST AND CONTINUITY TEST
- CABLE MUST BE PACKED INTO A PLASTIC BAG.

A	Prototype	Lucy Zheng	28/06/17
Rev.	Description	Appr.	Date

HARTING Customised Solutions

D-32427 Minden

Type	Number	Rev.	Page
TB	33 27 0001	A	1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[33272430500001](#) [33272431000002](#) [33272432000003](#)