

Han Megabit HMC insert fem. (shield-GND)




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 208 3117
Specification	Han Megabit HMC insert fem. (shield-GND)
HARTING eCatalogue	https://b2b.harting.com/09142083117

Identification

Category	Inserts
Specification	Han® Megabit HMC insert 2x 4 contacts 2 cable entries

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	8
Additional contacts	+ shielding
Details	With additional shield connection to the hinged frame Please order crimp contacts separately. Please order adapter module separately.
Details	Not suitable for hoods/housings low construction as well as Han-Modular® Eco, Han-Modular® Compact and Han-Modular® Twin.

Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm ²
Rated current	10 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Contact resistance, shielding	≤100 mΩ
Limiting temperature	-40 ... +85 °C



Pushing Performance

Technical characteristics

Mating cycles with other HMC components	≥10,000
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (shielding)	Zinc die-cast, nickel-plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	45 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440218 Module for industrial connectors (data)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09142083117