

Han3A RJ45 Cat5 PFT 8p



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 215 1100
Specification	Han3A RJ45 Cat5 PFT 8p
HARTING eCatalogue	https://b2b.harting.com/09452151100

Identification

Category	Connectors
Series	RJ45
Element	Panel feed through
Specification	Straight

Version

Size	Han [®] 3 A
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Fixing	Screwable in cover plates

Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated



Pushing Performance

Material properties

Colour (hood/housing)	Grey
RoHS	compliant with exemption
RoHS exemptions	6(a) / 6(a)-I: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight / Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight and in batch hot dip galvanised steel components containing up to 0,2 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	51.75 g
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27440101 Rectangular connectors (set)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09452151100](#)