



# DIN Power female low profile



## General information

|                                |                                                          |                   |
|--------------------------------|----------------------------------------------------------|-------------------|
| Design                         | complementary to IEC 60603-2, type: H female low profile |                   |
| No. of contacts                | 15                                                       |                   |
| Contact spacing                | 5,08mm or 2.54/ 10,16mm between the rows                 |                   |
| Test voltage                   | 3100V                                                    |                   |
| Contact resistance             | max. 8mOhm                                               |                   |
| Insulation resistance          | min. 10 <sup>10</sup> Ohm                                |                   |
| Working current                | 15A at 20°C (see derating diagram)                       |                   |
| Temperature range              | -55°C ... +125°C                                         |                   |
| Termination technology         | press-in                                                 |                   |
| Clearance                      | min. 4mm between contact termination pins                |                   |
| Creepage                       | min. 8,0mm                                               |                   |
| Insertion and withdrawal force | 15-pole max. 90N                                         |                   |
| Mating cycles                  | PL 1 acc. to IEC 60603-2                                 | 500 mating cycles |
|                                | PL 2 acc. to IEC 60603-2                                 | 400 mating cycles |
|                                | PL 3 acc. to IEC 60603-2                                 | 50 mating cycles  |
| UL file                        | E102079                                                  |                   |
| RoHS - compliant               | Yes                                                      |                   |
| Hot plugging                   | No                                                       |                   |

## Insulator material

|                                 |                                                     |
|---------------------------------|-----------------------------------------------------|
| Material                        | PBT (thermoplastics, glass fiber reinforcement 30%) |
| Color                           | RAL 7032 (light grey)                               |
| UL classification               | UL 94-V0                                            |
| Material group acc. IEC 60664-1 | II (400 < CTI < 600)                                |
| NFF classification              | I3, F4                                              |

## Contact material


|                          |              |
|--------------------------|--------------|
| Contact material         | Copper alloy |
| Plating termination zone | Ni           |
| Plating contact zone     | Ag           |

## Derating diagram acc. to IEC 60512-5 (Current carrying capacity)

The current carrying capacity is limited by maximum temperature of materials for inserts and contacts including terminals.


The current capacity curve is valid for continuous, non interrupted current loaded contacts of connectors when simultaneous power on all contacts is given, without exceeding the maximum temperature.

Control and test procedures according to DIN IEC 60512-5




## Low currents and voltages

Type H standard contacts have a silver plated surface. This precious metal has excellent conductive properties. In the course of a contact's lifetime, the silver surface generates a black oxide layer due to its affinity to sulphur. This layer is smooth and very thin and is partly interrupted when the contacts are mated and unmated, thus guaranteeing very low contact resistances. In the case of very low currents or voltages small changes to the transmitted signal may be encountered. In systems where such a change to the transmitted signal could lead to faulty functions and also in extremely aggressive environments, HARTING recommend the use of gold plated contacts. Below is a table derived from actual experiences.



## Recommended configuration of plated through holes for press-in termination

In addition to the hot-air-level (HAL), other PCB surfaces are getting more important. Due to their different properties - such as mechanical strength and coefficient of friction - we recommend the following configuration of PCB through holes.



|                                         |                |                |
|-----------------------------------------|----------------|----------------|
| Tin plated PCB (HAL) acc. to EN 60352-5 | Drilled hole Ø | 1,15±0,025 mm  |
|                                         | Cu             | min. 25 µm     |
|                                         | Sn             | max. 15 µm     |
| Chemical tin plated PCB                 | plated hole Ø  | 0,94 - 1,09 mm |
|                                         | Drilled hole Ø | 1,15±0,025 mm  |
|                                         | Cu             | min. 25 µm     |
| Gold /Nickel plated PCB                 | Sn             | min. 0,8 µm    |
|                                         | plated hole Ø  | 1,00 - 1,10 mm |
|                                         | Drilled hole Ø | 1,15±0,025 mm  |
|                                         | Cu             | min. 25 µm     |
|                                         | Ni             | 3-7 µm         |
|                                         | Au             | 0,05-0,12 µm   |
|                                         | plated hole Ø  | 1,00 - 1,10 mm |

## Assembly instruction

It is highly recommended to use HARTING press-in tools to ensure a reliable press-in process. Please refer to the catalogue for tools, machines and further information about the press-in process.

|                                                                                       |  |                                              |  |                                                  |  |                       |  |                             |  |                    |  |                                                          |  |
|---------------------------------------------------------------------------------------|--|----------------------------------------------|--|--------------------------------------------------|--|-----------------------|--|-----------------------------|--|--------------------|--|----------------------------------------------------------|--|
|  |  | All Dimensions in mm<br>Original Size DIN A3 |  | Scale<br>1:1                                     |  | Free size tol.        |  | Ref.                        |  |                    |  |                                                          |  |
|                                                                                       |  |                                              |  | Sub. DS 09062100102 / 26.07.2012                 |  |                       |  |                             |  |                    |  |                                                          |  |
|  |  | All rights reserved                          |  | Created by<br>WF-BATCH                           |  | Inspected by<br>AVRAM |  | Standardisation<br>HOFFMANN |  | Date<br>2013-11-05 |  | State<br>Final Release                                   |  |
|                                                                                       |  | Department EC PD - RO                        |  |                                                  |  |                       |  |                             |  |                    |  |                                                          |  |
| HARTING Electronics GmbH<br><br>D-32339 Espelkamp                                     |  |                                              |  | Title<br>DIN Power type H15 low-profile press-in |  |                       |  |                             |  |                    |  | Doc-Key / ECM-Nr.<br>100538959/UGD/001/A<br>500000066924 |  |
|                                                                                       |  |                                              |  | Type<br>DS                                       |  | Number<br>09062100102 |  |                             |  |                    |  | Rev.<br>A                                                |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[09062152890](#) [09062152854](#) [09062152856](#)