



Pushing Performance
Since 1945

Han 70A axial module, male 6-16mm²



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 14 002 2641 |
| Specification | Han 70A axial module, male 6-16mm ² |
| HARTING eCatalogue | https://b2b.harting.com/09140022641 |

Identification

| | |
|--------------------|------------------------------|
| Category | Modules |
| Series | Han-Modular [®] |
| Type of module | Han [®] 70 A module |
| Size of the module | Single module |
| Features | Finger safe contacts |

Version

| | |
|--------------------|-------------------------|
| Termination method | Axial screw termination |
| Gender | Male |
| Number of contacts | 2 |
| Details | Finger safe |

Technical characteristics

| | |
|-------------------------|--------------------------|
| Conductor cross-section | 6 ... 16 mm ² |
| Wire outer diameter | ≤10 mm |
| Rated current | 70 A |
| Rated voltage | 1,000 V |
| Rated impulse voltage | 8 kV |
| Pollution degree | 3 |
| Insulation resistance | >10 ¹⁰ Ω |
| Contact resistance | ≤0.5 mΩ |
| Stripping length | 11 ... 12 mm |



Pushing Performance
Since 1945

Technical characteristics

| | |
|----------------------|---------------------------|
| Tightening torque | 2 Nm @ 6 mm ² |
| | 3 Nm @ 10 mm ² |
| | 4 Nm @ 14 mm ² |
| | 4 Nm @ 16 mm ² |
| Limiting temperature | -40 ... +125 °C |
| Mating cycles | ≥500 |

Material properties

| | |
|---|---|
| Material (insert) | Polycarbonate (PC) |
| Colour (insert) | RAL 7032 (pebble grey) |
| Material (contacts) | Copper alloy |
| Surface (contacts) | Silver plated |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate Lead |
| ECHA SCIP number | 1e38d35d-d1be-4585-8e03-95faccd739bf |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead Nickel |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels | R22 (HL 1-3) R23 (HL 1-3) |

Specifications and approvals

| | |
|----------------|-----------------------------------|
| Specifications | IEC 60664-1 IEC 61984 |
| | UL 1977 ECBT2.E235076 |
| UL / CSA | UL 2237 PVVA2.E318390 |
| | CSA-C22.2 No. 182.3 PVVA8.E318390 |



Pushing Performance
Since 1945

Specifications and approvals

| | |
|-----------|--------|
| Approvals | DNV GL |
|-----------|--------|

Commercial data

| | |
|--------------------------------|---|
| Packaging size | 2 |
| Net weight | 32.8 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140019638 |
| ETIM | EC000438 |
| eCl@ss | 27440217 Module for industrial connectors (power/signals) |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09140022641](#)