



# AS85049/38 Straight Strain Relief Self-Locking or Non-Self-Locking

## CONNECTOR DESIGNATOR:

**H**MIL-DTL-38999 Series III & IV  
EN3645

**FOR NEW DESIGN  
USE AS85049/124**

Basic  
Part Number

**M85049/38**



Shell Size

**S****11****W**

**S** = Self-Locking  
Use Dash for Non-Self-Locking  
**N** = Non-Detented

### Material and Finish Designator

**A** = Aluminum, Black Anodize  
**N** = Aluminum, Electroless Nickel  
**S** = 300 Series Steel, Passivated  
**W** = Aluminum, 500 Hour Cadmium  
Olive Drab over Electroless Nickel



Note: Screw orientation shown is for non-self-locking configuration. Screws on self-locking configurations are on the same side/face of the clamp.

**TABLE I: Shell Size, Cable Entry and Backshell Dimensions**

| Shell Size | Shell Size Ref. | A Thread Class 2B | Ø E Max Self-Locking Only | F Max Self-Locking Only | H Max       | Cable Entry |             |     |  |  |  |
|------------|-----------------|-------------------|---------------------------|-------------------------|-------------|-------------|-------------|-----|--|--|--|
|            |                 |                   |                           |                         |             | Min         |             | Max |  |  |  |
| 9          | A               | M12 X 1 - 6H      | .858 (21.8)               | .91 (23.1)              | .85 (21.6)  | .098 (2.5)  | .234 (5.9)  |     |  |  |  |
| 11         | B               | M15 X 1 - 6H      | .984 (25.0)               | .91 (23.1)              | .90 (22.9)  | .153 (3.9)  | .234 (5.9)  |     |  |  |  |
| 13         | C               | M18 X 1 - 6H      | 1.157 (29.4)              | 1.01 (25.7)             | 1.10 (27.9) | .190 (4.8)  | .328 (8.3)  |     |  |  |  |
| 15         | D               | M22 X 1 - 6H      | 1.279 (32.5)              | 1.06 (26.9)             | 1.15 (29.2) | .260 (6.6)  | .457 (11.6) |     |  |  |  |
| 17         | E               | M25 X 1 - 6H      | 1.406 (35.7)              | 1.16 (29.5)             | 1.30 (33.0) | .283 (7.2)  | .614 (15.6) |     |  |  |  |
| 19         | F               | M28 X 1 - 6H      | 1.516 (38.5)              | 1.41 (35.8)             | 1.50 (38.1) | .325 (8.3)  | .634 (16.1) |     |  |  |  |
| 21         | G               | M31 X 1 - 6H      | 1.642 (41.7)              | 1.51 (38.4)             | 1.60 (40.6) | .343 (8.7)  | .698 (17.7) |     |  |  |  |
| 23         | H               | M34 X 1 - 6H      | 1.768 (44.9)              | 1.66 (42.2)             | 1.70 (43.2) | .381 (9.7)  | .823 (20.9) |     |  |  |  |
| 25         | J               | M37 X 1 - 6H      | 1.889 (48.0)              | 1.76 (44.7)             | 1.80 (45.7) | .418 (10.6) | .853 (21.7) |     |  |  |  |

## APPLICATION NOTES

1. Assembly to be identified with manufacturer's name and part number, space permitting.
2. Cable Entry is defined as the accommodation entry for the wire bundle or cable. Dimensions are not intended for inspection criteria.
3. For complete dimensions, see the applicable Military Specification.
4. Metric dimensions (mm) are in parentheses.

Dimensions in inches (millimeters) and are subject to change without notice.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Glenair:](#)

[GS85049/38-17M](#) [M85049/38N11A](#) [M85049/38N11N](#) [M85049/38N11S](#) [M85049/38N11W](#) [M85049/38N13S](#)  
[M85049/38N13W](#) [M85049/38N15A](#) [M85049/38N15S](#) [M85049/38N15W](#) [M85049/38N17S](#) [M85049/38N17W](#)  
[M85049/38N19A](#) [M85049/38N19N](#) [M85049/38N19S](#) [M85049/38N19W](#) [M85049/38N21A](#) [M85049/38N21S](#)  
[M85049/38N21W](#) [M85049/38N23A](#) [M85049/38N23N](#) [M85049/38N23S](#) [M85049/38N23W](#) [M85049/38N25N](#)  
[M85049/38N25S](#) [M85049/38N9A](#) [M85049/38N9N](#) [M85049/38N9S](#) [M85049/38N9W](#) [M85049/38S13A](#) [GS85049/38-09NF](#) [GS85049/38-13NF](#)