

M23 female-c 1,5mm (0,56–1,00mm²) Au



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 100 6212
Specification	M23 female-c 1,5mm (0,56–1,00mm²) Au
HARTING eCatalogue	https://b2b.harting.com/09151006212

Identification

Category	Contacts
Series	Circular connectors M23
Identification	Signal
Type of contact	Crimp contact
Description of the contact	1.5 mm

Version

Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.56 ... 1 mm²
Conductor cross-section	AWG 20 ... AWG 17
Operating current	≤10 A
Contact resistance	≤3 mΩ
Stripping length	4 mm

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



Pushing Performance

Material properties

China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

Commercial data

Packaging size	100
Net weight	0.19 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09151006212