
# MIL-DTL-38999 Series IV, Breech Coupling




38999/46 plug with EMI ground spring 38999/47 plug without EMI ground spring


QPL Part Number Development							
Sample Part Number	D38999/46	w	J	30	Р	N	
MIL-DTL-38999	38999/46 = Plug with EMI ground spring 38999/47 = Plug without EMI ground spring						
Class	F = Environmental, aluminum, electroless nickel, conductive, -65°C to +200°C W = Environmental, aluminum, cadmium olive drab, conductive, -65°C to +175°C G = Environmental, aluminum, electroless nickel, conductive, -65°C to +200°C (space-grade)						
Shell Size	B, C, D, E, F, G, H, J						
Insert Arrangement	Per MIL-STD-1560; See reference information section for details						
Contact Style	P = Pin Insert A = Pin Gender, Less Contacts S = Socket Insert B = Socket Gender, Less Contacts						
Polarization	N (Normal), A, B, C, D, K, L, M, R; see polarization positions table						











Polarization Positions									
	N	Α	В	С	D	K	L	М	R
Х	110°	100°	90°	80°	70°	120°	120°	120°	120°
Υ	250°	260°	270°	280°	290°	255°	265°	275°	285°

## COTS EQUIVALENT

# MIL-DTL-38999 Series IV, Breech Coupling



# 234-105-46 plug with EMI ground spring 234-105-47 plug without EMI ground spring

COTS Part Number Development							
Sample Part Numbe	234-105-46	NF	11	-35	Р	N	
Series / Basic Part No.	234-105-46 = Environmental plug with EMI ground spring 234-105-47 = Environmental plug without EMI ground spring						
Material/Finish	ME* = Aluminum, electroless nickel, conductive, -65°C to +200°C NF = Aluminum, cadmium olive drab, conductive, -65°C to +175°C MA† = Aluminum, electroless nickel, conductive, -65°C to +200°C (space-grade)						
Shell Size	11, 13, 15, 17, 19, 21, 23, 25						
Insert Arrangement	Per MIL-STD-1560; See reference information section for details						
Contact Designator	P = Pin Insert A = Pin Gender, Less Contacts S = Socket Insert B = Socket Gender, Less Contacts						
Polarization	N (Normal), A, B, C, D, K, L, M, R; see polarization positions table						

<sup>\*</sup> Plug connectors, styles 46 and 47, with ME finish supplied with hard anodized coupling nuts

<sup>†</sup> Connectors must be ordered with "MA" finish and modification code "-186T" to conform to the thermal vacuum outgassing requirements of Class G. Additional material/finish options are available, consult factory for ordering information.

Dimensions						
Shell Size	Shell Size Code	ØB Max	ØC Max	G Thread		
11	В	.776 (19.71)	1.047 (26.59)	M15 X 1.0-6g 0.100R		
13	С	.902 (22.91)	1.220 (30.99)	M18 X 1.0-6g 0.100R		
15	D	1.039 (26.39)	1.346 (34.19)	M22 X 1.0-6g 0.100R		
17	E	1.150 (29.21)	1.472 (37.39)	M25 X 1.0-6g 0.100R		
19	F	1.276 (32.41)	1.583 (40.21)	M28 X 1.0-6g 0.100R		
21	G	1.402 (35.61)	1.705 (43.31)	M31 X 1.0-6g 0.100R		
23	Н	1.528 (38.81)	1.831 (46.51)	M34 X 1.0-6g 0.100R		
25	J	1.650 (41.91)	1.957 (49.71)	M37 X 1.0-6g 0.100R		

Additional Material/Finish Options					
Finish Code	Description				
G2	Aluminum, anodize, hardcoat				
ZR Aluminum, zinc nickel, black (tri-valent cr)					
MT	Aluminum, nickel PTFE				

#### **NOTES**

- 1. Insert arrangements per MIL-STD-1560.
- Connector is supplied with contacts (including spares), insertion/removal tool and sealing plugs unless otherwise specified.
- 3. Blue color band indicates rear release retention system.

### **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

### Glenair:

```
D38999/46FJ19SA D38999/46WB5SN D38999/46WB99PA D38999/46FB35SA D38999/46FC4SN
D38999/46FC4PN D38999/46FG35SN D38999/46WB99SA D38999/46FC98PN D38999/46FJ35PN
D38999/46WB99SB D38999/46WC35SA D38999/46WE6SN D38999/46WG35SN D38999/46WG41PA
D38999/46WJ35SN D38999/46WC98PA D38999/46WC98SN D38999/46WD18PB D38999/46WH35SN
D38999/46WJ61PN D38999/46WJ61SA D38999/47FB35SA D38999/47WE6SN D38999/46FE35PN
D38999/46FG41PN D38999/46WC35PA D38999/46WE6PN D38999/46WE8PN D38999/46WG41PN
D38999/46FG11SN D38999/46WD35PA D38999/46WD5SA D38999/46WE35PA D38999/46WF11PN
D38999/47FD18PN D38999/46FB5SN D38999/46FD35SN D38999/46WB35PN D38999/46WB35SA
D38999/46WC35PN D38999/46WD18SD D38999/46WD19SN D38999/46WB99SD D38999/46WD5PN
D38999/46WD5SN D38999/46WE26SA D38999/46WD35SN D38999/46WE35PC D38999/46WF35PA
D38999/46WG11SN D38999/46WG41SB D38999/46WH35SD D38999/47FB35SN D38999/47FB5SN
D38999/47WE35SN D38999/46FC35SA D38999/46FD35SA D38999/46FE6SN D38999/46FG11PN
D38999/46FG16PN D38999/46WB35PA D38999/46WB5PA D38999/46WB99PC D38999/46FB35PN
D38999/46FD35PN D38999/46FG35SA D38999/46FJ35PB D38999/46WD18SN D38999/47WJ35SA
D38999/46FB35PA D38999/46FC35PN D38999/46FE26SN D38999/46FE35PA D38999/46FF32PN
D38999/46WB99PN D38999/46WC98PN D38999/46WD18SB D38999/46WE35SN D38999/46WF35PN
D38999/46WG16SN D38999/46WJ61PA D38999/46WJ61SN D38999/46FB35SN D38999/46FB99SN
D38999/46FC35SB D38999/46FE6PN D38999/46WB99PD D38999/46WB99SN D38999/46WD18PN
D38999/46WE26PA D38999/46WE8SN D38999/46WF32SN D38999/46WG16PN D38999/46WB99SC
D38999/46WC4SA D38999/46WD35SB D38999/46WE26SN D38999/46WE6BN D38999/46WF32PN
```