

770-001A1 and 770-003A1
Type 1 High-Performance Elastomer
90° Right Angle Lipped Adapter Shrink Boots



Type 1 High-Performance Elastomer Boots for Advanced Temperature and Chemical Tolerance



Semi-rigid high performance boots combine excellent resistance to fuels, oils and solvents with superior performance at extreme temperatures. Rated for 3000 hours continuous operation at +150° C, these 90° boots fit most standard boot adapters for circular connectors and aid in efficient routing of wire harnesses and cables. Material meets the requirements of VG95343 Type 6, BSG 198-5-DE, EN62329-102 and SAE AS5258 Type H. These boots are recommended for demanding applications such as military vehicles and petrochemical exploration. Boots come standard in black, see table below for optional colors.

- **-75° C to +150° C**
- **Excellent resistance to fuels, oils, solvents and heat.**
- **Ten available colors**

Boot Size	Part Number with Eyelet				Part Number without Eyelet			
	No Adhesive Lining	Pre-Coated with W1 Hi-Temp Hot-Melt Adhesive	Pre-Coated with W2 Standard Hot-Melt Adhesive	Pre-Coated with R Epoxy Adhesive	No Adhesive Lining	Pre-Coated with W1 Hi-Temp Hot-Melt Adhesive	Pre-Coated with W2 Standard Hot-Melt Adhesive	Pre-Coated with R Epoxy Adhesive
02	—	—	—	—	770-003A102	770-003A102W1	770-003A102W2	770-003A102R
03	770-001A103	770-001A103W1	770-001A103W2	770-001A103R	770-003A103	770-003A103W1	770-003A103W2	770-003A103R
04	770-001A104	770-001A104W1	770-001A104W2	770-001A104R	770-003A104	770-003A104W1	770-003A104W2	770-003A104R
05	770-001A105	770-001A105W1	770-001A105W2	770-001A105R	770-003A105	770-003A105W1	770-003A105W2	770-003A105R
06	770-001A106	770-001A106W1	770-001A106W2	770-001A106R	770-003A106	770-003A106W1	770-003A106W2	770-003A106R
07	770-001A107	770-001A107W1	770-001A107W2	770-001A107R	770-003A107	770-003A107W1	770-003A107W2	770-003A107R
08	770-001A108	770-001A108W1	770-001A108W2	770-001A108R	770-003A108	770-003A108W1	770-003A108W2	770-003A108R
09	770-001A109	770-001A109W1	770-001A109W2	770-001A109R	770-003A109	770-003A109W1	770-003A109W2	770-003A109R

Add "-DH" to the end of any part number for drain holes.

Add "-PP" to the end of any part number for potting ports.

Material Color Options for Type 1 High Performance Elastomer Only
Add Optional Color Mod Code to End of Any Type 1 Material Product

Mod Code	Color	Similar to (Reference)	Mod Code	Color	Similar to (Reference)
632 B	Blue	PANTONE 3005U	632 R	Red	PANTONE 1797U
632 E	Grey	FED-STD-595; #36270	632 T	Tan	FED-STD-595; #33446
632 G	Green	PANTONE 355U	632 W	White	FED-STD-595; #37875
632 P	Purple	FED-STD-595; #37100	632 Y	Yellow	PANTONE YELLOW U
632 O	Orange	FED-STD-595; #32300	Standard	Black	FED-STD-595; #37038

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[770-003A107](#) [770-003A103](#) [770-003A104](#) [770-003A105](#) [770-003A106](#) [770-003A108](#) [770-003A102](#) [770-001A109](#)