


891-003 and 891-004 Dual Row Nano Connector with Uninsulated Wire



Glenair Nano Connectors feature gold alloy TwistPin contacts. Contacts are precision-crimped to solid wire. These nanominiature connectors offer premium performance and reliability for demanding applications. Contact spacing is .025 inches. 1 amp current rating, DWV rating 250 volts AC. Wire gages #30 and #32 AWG.


TwistPin Contact System assures premium performance in demanding environments. The gold/platinum alloy contacts will stand up to years of exposure without corrosion.

Typical Applications include UAV's, satellites, missile systems and geophysical instruments.


How to Order Nano Connectors with Uninsulated Wire

Sample Part Number		891-003	-9P	A1	-0	D3	-.125	J
Series	891-003 Plug, Pin Contacts, Dual Row, Nanominiature, Uninsulated Wire 891-004 Receptacle, Socket Contacts, Dual Row, Nanominiature, Uninsulated Wire							
Insert Arrangement/ Contact Type	Plugs (891-003): 9P, 15P, 21P, 25P, 31P, 37P, 51P, 65P, 69P, 85P Receptacles (891-004): 9S, 15S, 21S, 25S, 31S, 37S, 51S, 65S, 69S, 85S							
Shell Material and Finish	A1 - Aluminum Shell, Cadmium Plating A2 - Aluminum Shell, Electroless Nickel Plating T - Titanium Shell, Unplated S - Stainless Steel Shell, Passivated							
Wire Gage	0 - #30 AWG 2 - #32 AWG							
Wire Type	D3 - Single Strand Copper Wire, Uninsulated, with Gold Plating							
Wire Length	.125, .250, .375, .500 , Wire Length in Inches							
Hardware	J - Jackscrew T - Female Thread Female Threads are available on plug connectors only if the shell material is titanium or stainless steel.							

Plug (Pin) Connector




"J" Jackscrew Option




"T" Female Thread Option
Titanium or Stainless Steel Shells Only

Receptacle (Socket) Connector



"T" Female Thread Option



"J" Jackscrew Option



Dimensions in inches (millimeters) and are subject to change without notice.





891-003 and 891-004 Dual Row Nano Connector with Uninsulated Wire

Table I: Dual Row Nano Dimensions

891-003 Plug (Pin) Connector



891-004 Receptacle (Socket) Connector



Layout	A		B BSC.		C BSC.		D		E BSC.		F Thread
	In. ± .005	mm. ± 0.13	In.	mm.	In.	mm.	In. ± .005	mm ± 0.13	In.	mm	
9P	.375	9.52	.270	6.86	.160	4.06	.125	3.18	.0575	1.46	#0-80 UNF
9S	.375	9.52	.270	6.86	.163	4.14	.125	3.18	.0575	1.46	#0-80 UNF
15P	.450	11.43	.345	8.76	.235	5.97	.125	3.18	.0575	1.46	#0-80 UNF
15S	.450	11.43	.345	8.76	.238	6.04	.125	3.18	.0575	1.46	#0-80 UNF
21P	.525	13.33	.420	10.67	.310	7.87	.125	3.18	.0575	1.46	#0-80 UNF
21S	.525	13.33	.420	10.67	.313	7.95	.125	3.18	.0575	1.46	#0-80 UNF
25P	.575	14.60	.470	11.94	.360	9.14	.125	3.18	.0575	1.46	#0-80 UNF
25S	.575	14.60	.470	11.94	.363	9.22	.125	3.18	.0575	1.46	#0-80 UNF
31P	.650	16.51	.545	13.84	.435	11.05	.125	3.18	.0575	1.46	#0-80 UNF
31S	.650	16.51	.545	13.84	.438	11.12	.125	3.18	.0575	1.46	#0-80 UNF
37P	.725	18.41	.620	15.75	.510	12.95	.125	3.18	.0575	1.46	#0-80 UNF
37S	.725	18.41	.620	15.75	.513	13.03	.125	3.18	.0575	1.46	#0-80 UNF
51P	.900	22.86	.795	20.19	.685	17.40	.125	3.18	.0575	1.46	#0-80 UNF
51S	.900	22.86	.795	20.19	.688	17.47	.125	3.18	.0575	1.46	#0-80 UNF
65P	1.075	27.30	.970	24.64	.860	21.84	.125	3.18	.0575	1.46	#0-80 UNF
65S	1.075	27.30	.970	24.64	.863	21.92	.125	3.18	.0575	1.46	#0-80 UNF
69P	1.125	28.57	1.020	25.91	.910	23.11	.125	3.18	.0575	1.46	#0-80 UNF
69S	1.125	28.57	1.020	25.91	.913	23.19	.125	3.18	.0575	1.46	#0-80 UNF
85P	1.377	34.97	1.246	31.65	1.110	28.19	.150	3.81	.070	1.78	#2-56 UNC
85S	1.377	34.97	1.246	31.65	1.113	28.27	.150	3.81	.070	1.78	#2-56 UNC

Dimensions in inches (millimeters) and are subject to change without notice.

© 2013 Glenair, Inc.

Series 89 Nano Catalog

U.S. CAGE Code 06324/0CA77

Printed in U.S.A.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[891-004-15SA2-0D3-.500J](#)