



Series 80 Mighty Mouse Standard Series Discrete Connector Offerings

The Series 80 Mighty Mouse Connector is designed for high-reliability commercial and aerospace/defense interconnect applications that require both robust environmental/EMI performance and reduced size and weight. The Series 80 Mighty Mouse Connector offers comparable performance to MIL-DTL-38999 Series interconnects with up to 71% weight and 52% size savings for similar contact layouts. The six versions of the product offer a variety of styles and features to suit just about any application.

Series 800



Series 801



Description	Original Mighty Mouse with UNF Threads	Double-Start ACME Thread
Notes	A general purpose connector for high-speed Ethernet switches, tactical equipment and instrumentation.	More rugged keys and threads compared to Series 800. Faster mating, slightly larger than Series 800.
Number of Contacts	1 to 37	1 to 130
Coupling	Threaded Coupling with 4 ½ Turns to Full Mate	Threaded Coupling with 1 ½ Turns to Full Mate
Water Immersion, Mated	MIL-STD-810 Method 512 1 Meter for 1 Hour	MIL-STD-810 Method 512 1 Meter for 1 Hour
EMI Shielding	Good	Good
Vibration and Shock	37 g's Random Vibration; 300 g's Shock	37 g's Random Vibration; 300 g's Shock
Mating Cycles	2000 Cycles	2000 Cycles
Electrical Performance	#12: 23 Amp, 1800 VAC #16: 13 Amp, 1800 VAC #20HD: 7.5 Amp, 1000 VAC #23: 5 Amp, 750 VAC	#12: 23 Amp, 1800 VAC #16: 13 Amp, 1800 VAC #20HD: 7.5 Amp, 1000 VAC #23: 5 Amp, 750 VAC
Proven Performance Applications	Commercial air frame sensors; UAV telemetry; Tactical computers; field radios	Military air frame; Dismounted soldier; Tactical ground weaponry; Avionic (FLIR) systems

**Series 80 Mighty Mouse
Standard Series
Discrete Connector Offerings**



Introduction

Series 802	Series 803	Series 804	Series 805
			
AquaMouse™ 3500 PSI	Bayonet	Push-Pull	Triple-Start ACME Thread
Rugged stainless steel, resists chemicals. For geophysical and underwater applications.	Quick-mating, light duty, general purpose. Not rated for immersion. 50 milliohms shell-to-shell resistance.	Breakaway connector for headsets and tactical equipment. Gold-plated spring for long mating life and superior EMI shielding.	"Clicker" ratchet mechanism and ground spring for military airframes and avionics boxes. Fast-mating, D38999 equivalent.
1 to 130	1 to 55	1 to 55	1 to 130
Threaded Coupling with UN Threads	Push-to-Mate, ¼ Turn to Lock	Quick-Disconnect	One Full Turn for Full Mate
1000 Feet Immersion in Salt Water	Splashproof	MIL-STD-810 Method 512 1 Meter for 1 Hour	MIL-STD-810 Method 512 1 Meter for 1 Hour
Good	Fair	Very Good	Excellent
37 g's Random Vibration; 300 g's Shock	37 g's Random Vibration; 300 g's Shock	37 g's Random Vibration; 300 g's Shock	37 g's Random Vibration; 300 g's Shock
2000 Cycles	250 Cycles Aluminum 2000 Cycles SST	2000 Cycles Aluminum 2000 Cycles SST	500 Cycles
#12: 23 Amp, 1800 VAC #16: 13 Amp, 1800 VAC #20HD: 7.5 Amp, 1000 VAC #23: 5 Amp, 750 VAC	#12: 23 Amp, 1800 VAC #16: 13 Amp, 1800 VAC #20HD: 7.5 Amp, 1000 VAC #23: 5 Amp, 750 VAC	#12: 23 Amp, 1800 VAC #16: 13 Amp, 1800 VAC #20HD: 7.5 Amp, 1000 VAC #23: 5 Amp, 750 VAC	#12: 23 Amp, 1800 VAC #16: 13 Amp, 1800 VAC #20HD: 7.5 Amp, 1000 VAC #23: 5 Amp, 750 VAC
Pipe line inspection equipment; Well logging; Amphibious vehicles; Unmanned submersibles	Soldier system radios; Autosport diagnostics; Airborne surveillance; Communication systems	Helmet breakaway connector; QDC battery; Missile applications; Weapon interconnects	Military air frame; Joint Strike Fighter

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[801-017Z19-19PA](#) [801-025-AA2M9-19NA-120](#) [805-011-07MT10-13SB](#) [805-011-07MT10-13SC](#) [805-011-07MT9-10SA](#)