

3-Axis RF Field Strength Meter



Description:

This meter is designed for measuring and monitoring Radio-Frequency electromagnetic field strength. The E200 is compact, durable and easy to use.

Features:

- The meter is a broadband device for monitoring high frequency radiation in the range from 50MHz to 3.5GHz
- Isotropic (non-directional) measurements of electromagnetic fields with three-channel measurement sensor
- Reports electrical and magnetic field strength and also power density
- Display the instantaneous, maximum or average values
- High dynamic range due to three-channel digital results processing
- Adjustable alarm threshold and memory function
- Easy & safe to use
- Low battery indicator "⎓"
- Store and recall up to 200 data sets
- Memory over-load indicator

Applications:

- Measurements of electric field strength in TEM cells and absorber rooms
- Mobile phone base station antenna radiation power density measurement
- Wireless communication applications (CW, TDMA, GSM, DECT)
- RF power measurement for transmitters
- Wireless LAN (Wi-Fi) detection, installation
- Spy camera, wireless bug finder
- Cellular phone radiation safety level
- Microwave oven leakage detection
- Personal living environment EMF safety



WARRANTY



Technical Specifications

Display Type	Liquid-crystal (LCD), 4-1/2 digits, maximum reading 19999
Measurement Method	Digital, triaxial measurement
Directional Type	Isotropic (triaxial)
Range Selection	One continuous range
Resolution	0.1mV/m, 0.1μA/m, 0.001μW/m ² , 0.001μW/cm ²
Setting Time	Typically 1.5s (0 to 90% measurement value)
Sample Rate	3 times per second
Units	mV/m, V/m, μA/m, mA/m, μW/m ² , mW/m ² , μW/cm ²
Display Value	Instantaneous measured value, maximum value, average value, or maximum average value
Audible Alarm	Buzzer
Alarm Function	Adjustable threshold with ON / OFF
Calibration Factor	Adjustable
Data Storage/Recall	200 Data Sets
Batteries	9V
Battery Life	Approximately 15 hours
Auto Power-Off	Default time 15 minutes. Adjustable threshold 0~99 minutes
Dimensions	60(L) x 60(W) x 195(H) mm
Weight	Approx. 200g (including battery)



Includes:

- E200 Meter
- User Manual
- 9V Battery
- Carrying Case

This instrument conforms to:

- **EN61326:** Electrical equipment for measurement, control and laboratory use.
- **IEC61000-4-2:** Electrostatic discharge immunity test.
- **IEC61000-4-3:** Radiated, radio-frequency, electromagnetic field immunity test.

Electrical Specifications

Sensor Type	Electrical field (E)
Frequency Range	50MHz ~ 3.5GHz
Specified Measurement Range	<ul style="list-style-type: none"> ▪ CW signal (f >50MHz): <ul style="list-style-type: none"> ○ 38mV/m to 20.00V/m ○ 53.0μA/m to 53.74mA/m ○ 0.1μW/m² to 1.089W/m² ○ 0.001μW/cm² to 108.9μW/cm²
Dynamic Range	<ul style="list-style-type: none"> ▪ Typically 75dB
Absolute error at 1V/m and 2.45GHz	<ul style="list-style-type: none"> ▪ 2.45GHz: ±1.0 dB
Frequency Response	<ul style="list-style-type: none"> ▪ Sensor taking into account the typical CAL factor: <ul style="list-style-type: none"> ○ ±2.4dB (50 MHz to 1.9 GHz) ○ ±1.0 dB (1.9 GHz to 3.5GHz)
Isotropy Deviation	<ul style="list-style-type: none"> ▪ Typically ±1.0 dB (2.45GHz)
Overload Limit	<ul style="list-style-type: none"> ▪ 0.42mW/cm², (11 V/m) per axis
Overload Limit	<ul style="list-style-type: none"> ▪ (0 to 50°C): ±0.2dB

Unless otherwise stated, the following specifications hold for these conditions:

- The meter is located in the far field of a source
- Sensor head is pointed towards the source
- Ambient Temperature: +23 °C, ±3°C
- Relative Humidity: 25%~75%



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Global Specialties:](#)

[E200](#)