



*Quality Products. Service Excellence.*

## Type 4, 4X Mild Steel and Stainless Steel Consolelet *Series 2000*

### Modular Console System



### Application

- Serves as an economical housing for operator interface applications.
- Provides an ideal sloped surface for mounting keyboards, switches, indicator lights, and/or dials.
- Provides panel mounting capabilities for a variety of applications.  
Generally used as a stand alone enclosure. Possible to put side by side with base on a single plinth (ie. 36" wide consolelet with 24" base with terminal all together on a 60" plinth).
- Optional casters (require plinth) allow for a completely mobile, NEMA rated work station.
- Smooth lines and clean edges provide an attractive, contemporary appearance.

### Standards

- UL 508A Type 3R, 4, 12 (Stainless Steel, add 4X)
- CSA Type 3R, 4, 12, 13 (Stainless Steel, add 4X)
- EIA RS-310-E
- Complies with
  - NEMA Type 3R, 4, 12 (Stainless Steel, add 4X)
  - IEC 60529, IP66

### Construction

- Formed 14 gauge steel bodies with 14 gauge steel door and lid.
- Also offered with formed 14 gauge 304 stainless steel bodies with 14 gauge 304 stainless steel door and lid.
- Smooth, continuously welded seams without knockouts or holes.
- Body stiffeners are provided where required for increased strength and rigidity.
- Offered in 4 widths 24", 36", 48" and 60".
- Has solid sides and back, solid door on front, 3 point adjustable lid on sloped (20°) top, and closed bottom with removable access panel.
- 24" and 36" widths have single door on the front whereas 48" and 60" widths have two outside hinged doors on the front.
- Doors can be hinged from either side on 24" and 36" units.
- Door profiles provide increased strength and are pre-punched to provide mounting options.
- Formed lip on enclosure excludes flowing liquids and contaminants.
- Slotted quarter turn oil-tight latches secure the door and lid, with optional tamper resistant and locking latches available.
- Stainless steel models utilize stainless steel hardware.
- Oil resistant gaskets are permanently secured.
- Features internal stud locations for mounting optional inner panel.
- A bonding screw is provided on the door and a grounding stud is provided in the enclosure.

### Finish

- Available in RAL 7035 light gray textured powder coating and natural stainless steel with a smooth, brushed finish.

Accessories

- Console Panel
- Quarter Turn Inserts and Keys
- Footrest
- Padlock Adaptor
- General Accessories
- Quarter Turn Assemblies
- Modular Plinth
- Climate Control
- Lighting

New and improved PDF part drawing files with more detail now available.

Click part number in table below to access PDF, DXF, and STEP files.

| RAL 7035 Light<br>Gray<br>Part No. | Stainless<br>Steel<br>Part No. | Enclosure |       |       |       |
|------------------------------------|--------------------------------|-----------|-------|-------|-------|
|                                    |                                | H1        | H2    | W     | D     |
| 2CLC2024                           | 2CSC2024                       | 30.36     | 38.03 | 24.00 | 17.30 |
| 2CLC2036                           | 2CSC2036                       | 30.36     | 38.03 | 36.00 | 17.30 |
| 2CLC2048                           | 2CSC2048                       | 30.36     | 38.03 | 48.00 | 17.30 |
| 2CLC2060                           | 2CSC2060                       | 30.36     | 38.03 | 60.00 | 17.30 |

Tags: Series 2000, Type 4X, Type 4, interface, console, modular, console, sloped, keyboard, plinth, stainless steel

Data subject to change without notice

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[2CLC2036](#) [2CLC2048](#) [2CLC2024](#) [2CSC2024](#) [2CSC2036](#) [2CSC2048](#) [2CSC2060](#) [2CLC2060](#)