



Pushing Performance  
Since 1945

# Han 40 EEE-M-C



Image is for illustration purposes only. Please refer to product description.

Part number	09 32 040 3001
Specification	Han 40 EEE-M-C
HARTING eCatalogue	<a href="https://b2b.harting.com/09320403001">https://b2b.harting.com/09320403001</a>

## Identification

Category	Inserts
Series	Han® EEE

## Version

Termination method	Crimp termination
Gender	Male
Size	16 B
Number of contacts	40
PE contact	Yes
Details	Please order crimp contacts separately.

## Technical characteristics

Conductor cross-section	0.14 ... 4 mm²
Conductor cross-section	AWG 26 ... AWG 12
Rated current	16 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	>10 <sup>10</sup> Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500



**Pushing Performance**  
Since 1945

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	1
Net weight	59 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140049307
ETIM	EC000438
eCl@ss	27440205 Contact insert for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09320403001](#)