

5


4

3


2

1

Edge mark on first conductor



Wire _____ Tinned copper
 Gauge _____ AWG 28/7 0,089 mm²
 Voltage rating _____ 300 Vr.m.s
 Current rating _____ 2,1A at 25°C
 Capacity unbalanced _____ 45,9 pF/m at 1 MHz
 Impedance unbalanced _____ 105 Ω
 Propagation delay _____ 4,9 ns/m nominal
 Insulation material _____ PVC
 Temperature rating _____ -20°C (operating) to +105°C
 _____ -30°C (static)
 Flammability rating _____ Flame retardant VW1
 Insulation resistance _____ 100 MΩ/km
 Approval _____ UL AWM style 2651

				Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	SEK 18 flat cable 40 poles	Maßstab/ Scale 10:1
			Detail.	20/10/05	JMDR			
			Insp.					
			Stand.					
EC01360	19/02/10	SC						
34400	18/09/07	PK						
33246	20/10/05	JMDR						
Mod.	Dat.	Name						

09 18 040 7004	100 m (328 feet)
09 18 040 7001	30,48 m (100 feet)
Part number	Length per reel

HARTING EURL
F-95972 Paris



TB 09 18 040 700X

Sub.

Blatt/ Page
1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[09180407001](#) [09180407004](#)