

Han HC-AX-PE-Kontaktstift



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 000 6156
Specification	Han HC-AX-PE-Kontaktstift
HARTING eCatalogue	https://b2b.harting.com/09110006156

Identification

Category	Contacts
Series	TC 350
Type of contact	PE contact

Version

Termination method	Axial screw termination
Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	35 ... 70 mm ²
Operating current	≤350 A
Contact resistance	≤0.2 mΩ
Limiting temperature	-40 ... +125 °C
Stripping length	19 ... 20 mm
Tightening torque	8 Nm @ 35 mm ² 10 Nm @ 50 mm ² 12 Nm @ 70 mm ²
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption



Pushing Performance

Material properties

RoHS exemptions	6(a) / 6(a)-I: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight / Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight and in batch hot dip galvanised steel components containing up to 0,2 % lead by weight 6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

Commercial data

Packaging size	1
Net weight	133.72 g
Country of origin	Romania
European customs tariff number	85359000
eCl@ss	27440204 Contact for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09110006156