







1	2	3	4	5	6	7	8																																																				
A	<div><div></div><div>DIN power male connector - SMC</div><div><div>RoHS</div><div>compliant</div><div></div></div></div>			<div>Soldering instructions</div> <div>SMC (Surface Mount Compatible) connectors are designed to be used in a reflow oven together with other SMD (Surface Mount Device) components. In this process, called as well „Pin in Hole Intrusive Reflow“, the connectors are inserted into plated through holes in a comparable way to conventional component mounting. All other components can be assembled on the pcb surface. The length of the connector contacts should be such that they protrude by no more than 1.5 millimetres after insertion to the pcb. Each contact collects solder on its tip as it penetrates the solder paste in the hole. So if the contact is too long, this solder would no longer be able to reflow back into the plated through hole by capillary action during the soldering process, therefore the quality of the soldered connection would suffer as a result.</div>				A																																																			
B	<div>General information</div> <table><tr><td>Design</td><td>IEC 60603-2</td><td>types: D, E male</td></tr><tr><td>No. of contacts</td><td>max. 48</td><td></td></tr><tr><td>Contact spacing</td><td>5,08 mm</td><td>(2,54 mm or 5,08 mm on termination side for type E angled)</td></tr><tr><td>Test voltage</td><td>1550V</td><td></td></tr><tr><td>Contact resistance</td><td>max. 15mOhm</td><td></td></tr><tr><td>Insulation resistance</td><td>min. 10¹²Ohm</td><td></td></tr><tr><td>Working current</td><td>max. 6 A at 20°C (see derating diagram)</td><td></td></tr><tr><td>Temperature range</td><td>-55°C ... +125°C max. 15s at 240°C for reflow soldering</td><td></td></tr><tr><td>Termination technology</td><td>SMC (Surface Mount Compatible) with solder pins</td><td></td></tr><tr><td>Clearance</td><td>min. 3,0 mm</td><td>(min. 1,6 mm for 2,54 mm contact spacing at type E angled)</td></tr><tr><td>Creepage</td><td>min. 3,0 mm</td><td></td></tr><tr><td>Insertion and withdrawal force</td><td>32pol. max. 50N 48pol. max. 75N</td><td></td></tr><tr><td>Mating cycles</td><td>- PL1 acc. to IEC 60 603-2 => - PL2 acc. to IEC 60 603-2 => - PL3 acc. to IEC 60 603-2 =></td><td>500 mating cycles 400 mating cycles 50 mating cycles</td></tr><tr><td>UL file</td><td>E102079</td><td></td></tr><tr><td>RoHS - compliant</td><td>Yes</td><td></td></tr><tr><td>Leadfree</td><td>Yes</td><td></td></tr><tr><td>Hot plugging</td><td>No</td><td></td></tr></table>			Design	IEC 60603-2	types: D, E male	No. of contacts	max. 48		Contact spacing	5,08 mm	(2,54 mm or 5,08 mm on termination side for type E angled)	Test voltage	1550V		Contact resistance	max. 15mOhm		Insulation resistance	min. 10 ¹² Ohm		Working current	max. 6 A at 20°C (see derating diagram)		Temperature range	-55°C ... +125°C max. 15s at 240°C for reflow soldering		Termination technology	SMC (Surface Mount Compatible) with solder pins		Clearance	min. 3,0 mm	(min. 1,6 mm for 2,54 mm contact spacing at type E angled)	Creepage	min. 3,0 mm		Insertion and withdrawal force	32pol. max. 50N 48pol. max. 75N		Mating cycles	- PL1 acc. to IEC 60 603-2 => - PL2 acc. to IEC 60 603-2 => - PL3 acc. to IEC 60 603-2 =>	500 mating cycles 400 mating cycles 50 mating cycles	UL file	E102079		RoHS - compliant	Yes		Leadfree	Yes		Hot plugging	No		<div>Quantity of solder paste</div> <div>Before the components are assembled, solder paste must be applied to all the solder pads (for connecting surface-mount components) and the plated through holes. To ensure that the plated through holes are completely filled, significantly more solder paste must be applied than traditional solder pads on the pcb surface. There are numerous calculation methods available which are complicated to apply. The following rule of thumb has proved valuable in practice: VPaste = 2(VH - VP) in which: VPaste = Required volume of solder paste VH = Volume of the plated through hole VP = Volume of the connector termination in the hole Comment: the multiplier "2" compensates for solder paste shrinkage during soldering. For this purpose, it was assumed that 50 % of the paste consists of the actual solder, the other 50 % being soldering aids.</div>				B
Design	IEC 60603-2	types: D, E male																																																									
No. of contacts	max. 48																																																										
Contact spacing	5,08 mm	(2,54 mm or 5,08 mm on termination side for type E angled)																																																									
Test voltage	1550V																																																										
Contact resistance	max. 15mOhm																																																										
Insulation resistance	min. 10 ¹² Ohm																																																										
Working current	max. 6 A at 20°C (see derating diagram)																																																										
Temperature range	-55°C ... +125°C max. 15s at 240°C for reflow soldering																																																										
Termination technology	SMC (Surface Mount Compatible) with solder pins																																																										
Clearance	min. 3,0 mm	(min. 1,6 mm for 2,54 mm contact spacing at type E angled)																																																									
Creepage	min. 3,0 mm																																																										
Insertion and withdrawal force	32pol. max. 50N 48pol. max. 75N																																																										
Mating cycles	- PL1 acc. to IEC 60 603-2 => - PL2 acc. to IEC 60 603-2 => - PL3 acc. to IEC 60 603-2 =>	500 mating cycles 400 mating cycles 50 mating cycles																																																									
UL file	E102079																																																										
RoHS - compliant	Yes																																																										
Leadfree	Yes																																																										
Hot plugging	No																																																										
C								C																																																			
D	<div>Insulator material</div> <table><tr><td>Material</td><td>PCT (thermoplastics, glass fiber reinforcement 30%)</td></tr><tr><td>Colour</td><td>natural-colored, color deviations and speckles permitted</td></tr><tr><td>UL classification</td><td>UL 94-V0</td></tr><tr><td>Material group acc. to IEC 60664-1</td><td>II (400 ≤ CTI < 600)</td></tr><tr><td>NFF classification</td><td>I3, F3</td></tr></table>			Material	PCT (thermoplastics, glass fiber reinforcement 30%)	Colour	natural-colored, color deviations and speckles permitted	UL classification	UL 94-V0	Material group acc. to IEC 60664-1	II (400 ≤ CTI < 600)	NFF classification	I3, F3	<div>Cross section of solder pins</div> <div></div>				D																																									
Material	PCT (thermoplastics, glass fiber reinforcement 30%)																																																										
Colour	natural-colored, color deviations and speckles permitted																																																										
UL classification	UL 94-V0																																																										
Material group acc. to IEC 60664-1	II (400 ≤ CTI < 600)																																																										
NFF classification	I3, F3																																																										
E	<div>Contact material</div> <table><tr><td>Contact material</td><td>Copper alloy</td></tr><tr><td>Plating termination zone</td><td>Sn over Ni</td></tr><tr><td>Plating contact zone</td><td>Au over PdNi over Ni</td></tr></table>			Contact material	Copper alloy	Plating termination zone	Sn over Ni	Plating contact zone	Au over PdNi over Ni					E																																													
Contact material	Copper alloy																																																										
Plating termination zone	Sn over Ni																																																										
Plating contact zone	Au over PdNi over Ni																																																										
F	<div>Derating diagram acc. to IEC 60512-5 (Current carrying capacity)</div> <div>The current carrying capacity is limited by maximum temperature of materials for inserts and contacts including terminals. The current capacity curve is valid for continuous, non interrupted current loaded contacts of connectors when simultaneous power on all contacts is given, without exceeding the maximum temperature. Control and test procedures according to DIN IEC 60512-5</div> <div></div>			<div><div><div></div><div>All rights reserved Department EC PD - DE</div></div><div>HARTING Electronics GmbH D-32339 Espelkamp</div></div> <div><div></div><div>All Dimensions in mm Original Size DIN A3</div></div> <div><div>Scale 1:1</div><div>Free size tol.</div></div> <div><div>Created by HAGEMEYERE</div><div>Inspected by TADJE</div><div>Standardisation HOFFMANN</div></div> <div><div>Date 2014-08-11</div><div>State Final Release</div></div> <div><div>Title DIN power male connector - SMC</div><div>Type DS</div><div>Number 09041030201</div></div> <div><div>Doc-Key / ECM-Nr. 100580512/UGD/000/A 500000076067</div><div>Rev. A</div><div>Page 1/1</div></div>																																																							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09043326919