


1	2	3	4	5	6	7	8																												
A	 Han® 3A RJ45 Hybrid Cat6 RoHS compliant 							A																											
General information								B																											
<table><tr><td>Design</td><td>Hybrid connector for Ethernet communication and power supply</td></tr><tr><td>Product standard</td><td>IEC 61076-3-106 (Variant 5)</td></tr><tr><td>No. of contacts</td><td>8 + 4 (2x4 for Ethernet + 4x power)</td></tr></table>								Design	Hybrid connector for Ethernet communication and power supply	Product standard	IEC 61076-3-106 (Variant 5)	No. of contacts	8 + 4 (2x4 for Ethernet + 4x power)																						
Design	Hybrid connector for Ethernet communication and power supply																																		
Product standard	IEC 61076-3-106 (Variant 5)																																		
No. of contacts	8 + 4 (2x4 for Ethernet + 4x power)																																		
B	<table><tr><td>Transmission rate</td><td>10 / 100 Mbit/s and 1 / 2,5 / 5 / 10 Gbit/s</td></tr><tr><td>Transmission performance</td><td>Category 6/6A / Class EA up to 500 MHz acc. to ISO/IEC 11801:2002, EN 50173-1</td></tr><tr><td>Shielding</td><td>Fully shielded, 360° shielding contact</td></tr><tr><td>Degree of protection</td><td>IP65/67</td></tr><tr><td>Mating cycles</td><td>Min. 500</td></tr><tr><td>UL certification</td><td>E 102079</td></tr><tr><td>RoHS – complainant</td><td>yes</td></tr><tr><td>Lead free</td><td>yes</td></tr></table>							Transmission rate	10 / 100 Mbit/s and 1 / 2,5 / 5 / 10 Gbit/s	Transmission performance	Category 6/6A / Class EA up to 500 MHz acc. to ISO/IEC 11801:2002, EN 50173-1	Shielding	Fully shielded, 360° shielding contact	Degree of protection	IP65/67	Mating cycles	Min. 500	UL certification	E 102079	RoHS – complainant	yes	Lead free	yes												
Transmission rate	10 / 100 Mbit/s and 1 / 2,5 / 5 / 10 Gbit/s																																		
Transmission performance	Category 6/6A / Class EA up to 500 MHz acc. to ISO/IEC 11801:2002, EN 50173-1																																		
Shielding	Fully shielded, 360° shielding contact																																		
Degree of protection	IP65/67																																		
Mating cycles	Min. 500																																		
UL certification	E 102079																																		
RoHS – complainant	yes																																		
Lead free	yes																																		
C	Cable specification and termination details for the plug side							C																											
<table><tr><td>Cable diameter (plug)</td><td>6 to 12 mm</td></tr></table>								Cable diameter (plug)	6 to 12 mm																										
Cable diameter (plug)	6 to 12 mm																																		
Ethernet																																			
IDC types (Cat. 6)																																			
<table><tr><td>Conductor cross section</td><td>AWG 27 to AWG 22 (solid and stranded)</td></tr><tr><td>Conductor diameter</td><td>Max. 1,6 mm</td></tr></table>								Conductor cross section	AWG 27 to AWG 22 (solid and stranded)	Conductor diameter	Max. 1,6 mm																								
Conductor cross section	AWG 27 to AWG 22 (solid and stranded)																																		
Conductor diameter	Max. 1,6 mm																																		
Piercing types (Cat. 6A)																																			
D	<table><tr><td>Conductor cross section</td><td>AWG 28/7 to AWG 24/7 (stranded)</td></tr><tr><td>Conductor diameter</td><td>Max. 1,05 mm</td></tr></table>							Conductor cross section	AWG 28/7 to AWG 24/7 (stranded)	Conductor diameter	Max. 1,05 mm																								
Conductor cross section	AWG 28/7 to AWG 24/7 (stranded)																																		
Conductor diameter	Max. 1,05 mm																																		
<table><tr><td>Power</td><td>IDC contacts 4x 1,5 mm² (stranded)</td></tr></table>								Power	IDC contacts 4x 1,5 mm² (stranded)																										
Power	IDC contacts 4x 1,5 mm² (stranded)																																		
Panel feed-through																																			
E	<table><tr><td>Mating interface extern:</td><td>RJ45 acc. to IEC 60603-7 for Ethernet and 4 power contacts</td></tr><tr><td>Mating interface intern:</td><td>RJ45 acc. to IEC 60603-7 for Ethernet and 4 PCB terminals</td></tr></table>							Mating interface extern:	RJ45 acc. to IEC 60603-7 for Ethernet and 4 power contacts	Mating interface intern:	RJ45 acc. to IEC 60603-7 for Ethernet and 4 PCB terminals																								
Mating interface extern:	RJ45 acc. to IEC 60603-7 for Ethernet and 4 power contacts																																		
Mating interface intern:	RJ45 acc. to IEC 60603-7 for Ethernet and 4 PCB terminals																																		
Power																																			
<table><tr><td>Conductor cross section PCB terminal</td><td>0,5 to 2,5mm² (solid and stranded)</td></tr></table>								Conductor cross section PCB terminal	0,5 to 2,5mm² (solid and stranded)																										
Conductor cross section PCB terminal	0,5 to 2,5mm² (solid and stranded)																																		
F	<table><tr><td rowspan="4"></td><td colspan="2">All rights reserved</td><td>Created by</td><td>Inspected by</td><td>Standardisation</td><td>Date</td><td>State</td></tr><tr><td colspan="2">Department EC PD – RO</td><td>DRAGHICI</td><td>AVRAM</td><td>HOFFMANN</td><td>2017-05-03</td><td>Final Release</td></tr><tr><td colspan="2" rowspan="2">HARTING Electronics GmbH D-32339 Espelkamp</td><td colspan="4">Title Han® 3A RJ45 Hybrid Cat6</td><td>Doc-Key / ECM-Nr. 100637182/UGD/000/A 500000109451</td></tr><tr><td>Type DS</td><td colspan="2">Number 09452251760</td><td>Rev. A</td><td>Page 1/3</td></tr></table>								All rights reserved		Created by	Inspected by	Standardisation	Date	State	Department EC PD – RO		DRAGHICI	AVRAM	HOFFMANN	2017-05-03	Final Release	HARTING Electronics GmbH D-32339 Espelkamp		Title Han® 3A RJ45 Hybrid Cat6				Doc-Key / ECM-Nr. 100637182/UGD/000/A 500000109451	Type DS	Number 09452251760		Rev. A	Page 1/3	F
	All rights reserved		Created by	Inspected by	Standardisation	Date	State																												
	Department EC PD – RO		DRAGHICI	AVRAM	HOFFMANN	2017-05-03	Final Release																												
	HARTING Electronics GmbH D-32339 Espelkamp		Title Han® 3A RJ45 Hybrid Cat6				Doc-Key / ECM-Nr. 100637182/UGD/000/A 500000109451																												
			Type DS	Number 09452251760		Rev. A	Page 1/3																												
1	2	3	4	5	6	7	8																												

1	2	3	4	5	6	7	8
A							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09451251760](#) [09451151760](#) [09451251720](#) [09451151720](#) [09451001760](#) [09452151765](#) [09452151760](#)
[09452151761](#) [09452251760](#) [09451001720](#) [09452251761](#)