

M12 D-cod 4-pol st/st m/m Rail 16m



Image is for illustration purposes only. Please refer to product description.

Part number	09 48 222 2011 160
Specification	M12 D-cod 4-pol st/st m/m Rail 16m
HARTING eCatalogue	https://b2b.harting.com/09482222011160

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 D-coding
	Male Straight
	Overmoulded
Connector 2	M12 D-coding
	Male Straight
	Overmoulded
Type of cable	Copper cable (round)
Description of the cable	for railway applications

Version

Cable length	16 m
Number of cores	4
Core structure	4x AWG 22/7
Coding	D-coding

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s
	100 Mbit/s
Limiting temperature	-40 ... +85 °C unmoved
	-25 ... +70 °C moved



Pushing Performance
Since 1945

Technical characteristics

Cable diameter	6.6 mm \pm 0.2 mm
Minimum bending radius	6x Cable diameter (repeated bending)
	5x Cable diameter (singular bending)
Impedance	100 Ω \pm 5 %

Material properties

Material (cable)	Elastomer
Colour (cable)	Black

Specifications and approvals

Specifications	EN 45545-2
----------------	------------

Commercial data

Packaging size	1
Net weight	1,089 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140247864
ETIM	EC002599
eCl@ss	27060390 Ready-made data cable (unspecified)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09482222011160](#)