



Pushing Performance
Since 1945

Han C module, crimp male



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 14 003 3002 |
| Specification | Han C module, crimp male |
| HARTING eCatalogue | https://b2b.harting.com/09140033002 |

Identification

| | |
|--------------------|---------------|
| Category | Modules |
| Series | Han-Modular® |
| Type of module | Han® C module |
| Size of the module | Single module |

Version

| | |
|--------------------|---|
| Termination method | Crimp termination |
| Gender | Male |
| Number of contacts | 3 |
| Details | Please order crimp contacts separately. |

Technical characteristics

| | |
|--------------------------|--|
| Conductor cross-section | 1.5 ... 6 mm² |
| Wire outer diameter | ≤4.8 mm 4.8 ... 7.8 mm Stripping length 12 mm |
| Rated current | 40 A |
| Rated voltage | 690 V |
| Rated impulse voltage | 8 kV |
| Pollution degree | 3 |
| Rated current acc. to UL | 40 A |
| Rated voltage acc. to UL | 600 V |
| Insulation resistance | >10 ¹⁰ Ω |



Pushing Performance
Since 1945

Technical characteristics

| | |
|---------------------------|---|
| Stripping length | 9.5 mm |
| | 12 mm Wire outer diameter > 4.8 mm |
| Limiting temperature | -40 ... +125 °C |
| Mating cycles | ≥10,000 |
| Note on the mating cycles | Mating cycles with other HMC components |

Material properties

| | |
|---|------------------------|
| Material (insert) | Polycarbonate (PC) |
| Colour (insert) | RAL 7032 (pebble grey) |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Not contained |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels | R22 (HL 1-3) |
| | R23 (HL 1-3) |

Specifications and approvals

| | |
|----------------|-----------------------|
| Specifications | IEC 60664-1 |
| | IEC 61984 |
| UL / CSA | UL 1977 ECBT2.E235076 |
| Approvals | DNV GL |

Commercial data

| | |
|--------------------------------|---------------|
| Packaging size | 2 |
| Net weight | 4 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140020054 |
| ETIM | EC000438 |



Pushing Performance
Since 1945

Commercial data

eCl@ss

27440217 Module for industrial connectors (power/signals)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09140033002](#)