

## Han 10EMC/B-HBM-Rear Fit-DL



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 62 810 0315  |
| Specification      | Han 10EMC/B-HBM-Rear Fit-DL   |
| HARTING eCatalogue | <a href="https://b2b.harting.com/09628100315">https://b2b.harting.com/09628100315</a> |

### Identification

|                             |                                |
|-----------------------------|--------------------------------|
| Category                    | Hoods/Housings                 |
| Series of hoods/housings    | Han <sup>®</sup> EMC/B         |
| Type of hood/housing        | Bulkhead mounted housing       |
| Description of hood/housing | External seal<br>Rear mounting |
| Type                        | Low construction               |

### Version

|                            |  |
|----------------------------|--|
| Size                       | 10 B   |
| Locking type               | Double locking lever                           |
| Han-Easy Lock <sup>®</sup> | Yes  |
| Field of application       | Hoods/Housings for higher EMC requirements     |
| Pack contents              | Mounting frame is included within the delivery |

### Technical characteristics

|  |  |
|--|--|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP66   |
| Type rating acc. to UL 50 / UL 50E     | 4<br>12  |

### Material properties

|                         |                    |
|-------------------------|--------------------|
| Material (hood/housing) | Aluminium die-cast |
| Surface (hood/housing)  | Uncoated           |



**Pushing Performance**  
Since 1945

## Material properties

|  |   |
|--|---|
| Colour (hood/housing)                                      | Unpainted   |
| Material (seal)  | NBR   |
| Material (locking)   | Polycarbonate (PC)<br>Stainless steel                     |
| Colour (locking)   | RAL 7037 (dust grey)                                      |
| Material (accessories)                                     | Polyamide (PA)<br>Stainless steel                         |
| Material flammability class acc. to UL 94 (locking levers) | V-0   |
| RoHS   | compliant   |
| ELV status   | compliant   |
| China RoHS   | e   |
| REACH Annex XVII substances                                | Not contained   |
| REACH ANNEX XIV substances                                 | Not contained   |
| REACH SVHC substances                                      | Yes   |
| REACH SVHC substances                                      | Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate |
| Fire protection on railway vehicles                        | EN 45545-2 (2020-08)                                      |
| Requirement set with Hazard Levels                         | R22 (HL 1-3)<br>R23 (HL 1-3)                              |

## Specifications and approvals

|           |  |
|-----------|--|
| UL / CSA  | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | CE<br>DNV GL   |

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1  |
| Net weight                     | 157.1 g                                  |
| Country of origin              | China                                    |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140171749                            |
| ETIM                           | EC000437                                 |
| eCl@ss                         | 27440202 Shell for industrial connectors |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09628100315](#)