



Pushing Performance  
Since 1945

# Han DD Quad module female



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 042 3101
Specification	Han DD Quad module female
HARTING eCatalogue	<a href="https://b2b.harting.com/09140423101">https://b2b.harting.com/09140423101</a>

## Identification

Category	Modules
Series	Han-Modular®
Type of module	Han DD® Quad module
Size of the module	Double module

## Version

Termination method	Crimp termination
Gender	Female
Number of contacts	42
Details	Please order crimp contacts separately.

## Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm²
Conductor cross-section [AWG]	AWG 26 ... AWG 14
Wire outer diameter	≤3.7 mm
Rated current	10 A
Rated voltage	150 V
Rated impulse voltage	2.5 kV
Pollution degree	3
Rated voltage acc. to UL	250 V
Insulation resistance	>10 <sup>10</sup> Ω
Limiting temperature	-40 ... +125 °C



**Pushing Performance**  
Since 1945

## Technical characteristics

Mating cycles	≥500
---------------	------

## Material properties

Material (insert)	Polycarbonate (PC)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

## Commercial data

Packaging size	1
Net weight	22 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140021464
ETIM	EC000438
eCl@ss	27440217 Module for industrial connectors (power/signals)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09140423101](#)