

## DSUB SVMASSDPANG73-254 15PPL2GCSLK4-40HT



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 65 266 6813  |
| Specification      | DSUB SVMASSDPANG73-254<br>15PPL2GCSLK4-40HT   |
| HARTING eCatalogue | <a href="https://b2b.harting.com/09652666813">https://b2b.harting.com/09652666813</a> |

### Identification

|                            |                   |
|----------------------------|-------------------|
| Category                   | Connectors        |
| Series                     | D-Sub             |
| Identification             | Standard          |
| Element                    | Connector         |
| Description of the contact | Stamped<br>Angled |

### Version

|                    |   |
|--------------------|---|
| Termination method | Reflow soldering termination (THR)            |
| Gender             | Male  |
| Size               | D-Sub 2                                       |
| Connection type    | Motherboard to daughtercard                   |
| Number of contacts | 15  |
| Termination length | 2.9 mm  |
| Locking type       | Fixing flange with fitted screw lock 4-40 UNC |

### Technical characteristics

|                                    |                     |
|------------------------------------|---------------------|
| Distance between rows              | 2.54 mm             |
| Contact spacing (termination side) | 2.74 mm             |
| Rated current                      | 6.5 A               |
| Clearance distance                 | ≥1 mm               |
| Creepage distance                  | ≥1 mm               |
| Insulation resistance              | >10 <sup>10</sup> Ω |



**Pushing Performance**  
Since 1945

## Technical characteristics

|                                  |   |
|----------------------------------|---|
| Contact resistance               | ≤10 mΩ  |
| Tightening torque                | ≤0.4 Nm Locking screw   |
| Limiting temperature             | -55 ... +125 °C (during reflow soldering max. +240 °C for 15 s) |
| Insertion force                  | ≤50 N   |
| Withdrawal force                 | ≥4.5 N<br>≤33 N   |
| Performance level                | 2<br>acc. to CECC 75301-802                                     |
| Mating cycles                    | ≥250  |
| Test voltage U <sub>r.m.s.</sub> | 1 kV  |
| Isolation group                  | II (400 ≤ CTI < 600)  |
| PCB thickness                    | ≥1.6 mm   |
| Installation height              | 7.3 mm  |
| Hot plugging                     | No  |

## Material properties

|   |  |
|---|--|
| Material (insert)                         | Thermoplastic resin, glass-fibre filled (PCT)<br>Shell: steel, nickel plated |
| Colour (insert)                           | Grey   |
| Material (contacts)                       | Copper alloy   |
| Surface (contacts)                        | Noble metal over Ni  |
| Material flammability class acc. to UL 94 | V-0  |
| RoHS                                      | compliant with exemption   |
| RoHS exemptions                           | 6(c): Copper alloy containing up to 4 % lead by weight                       |
| ELV status                                | compliant with exemption   |
| China RoHS                                | 50   |
| REACH Annex XVII substances               | Not contained  |
| REACH ANNEX XIV substances                | Not contained  |
| REACH SVHC substances                     | Yes  |
| REACH SVHC substances                     | Lead   |
| ECHA SCIP number                          | ecef7555-f643-4ceb-a337-fc54762297f1   |
| California Proposition 65 substances      | Yes  |
| California Proposition 65 substances      | Lead<br>Nickel   |
| Fire protection on railway vehicles       | EN 45545-2 (2020-08)   |



**Pushing Performance**  
Since 1945

Material properties

Requirement set with Hazard Levels R26

Specifications and approvals

|                |           |
|----------------|-----------|
| Specifications | DIN 41652 |
|----------------|-----------|

Commercial data

|                                |                        |
|--------------------------------|------------------------|
| Packaging size                 | 1                      |
| Net weight                     | 12 g                   |
| Country of origin              | Romania                |
| European customs tariff number | 85366990               |
| GTIN                           | 5713140078178          |
| ETIM                           | EC001136               |
| eCl@ss                         | 27440214 D-Sub coupler |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09652666813](#)