



Pushing Performance  
Since 1945

# Han-Yellock side entry M20 white



Image is for illustration purposes only. Please refer to product description.

Part number	11 12 300 1510
Specification	Han-Yellock side entry M20 white
HARTING eCatalogue	<a href="https://b2b.harting.com/11123001510">https://b2b.harting.com/11123001510</a>

## Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Shell
Description of hood/housing	White

## Version

Size	Han-Yellock® 30
Version	Side entry
Cable entry	1x M20
Locking type	Push button
Field of application	Hoods/housings for industrial applications

## Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Un-/locking temperature	-10 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67

## Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 1013 (white)



**Pushing Performance**  
Since 1945

## Material properties

Material (locking)	Polyamide (PA) Stainless steel
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	119 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140110069
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[11123001510](#)