



har-flexicon terminal block horizontal, screwing



General information

PCB Terminal Block						
Design						
Type	3,50/3,81 TTSH	5,00 TTSH 1,5mm ²	5,00 TTSH 2,5mm ²	7,50 TTSH	10,16 TTSH	15,00 TTSH
Part numbers	1402xx14402xxx 1402xx15402xxx	1402xx16402xxx	1402xx16404xxx	1402xx21404xxx	1402xx25402xxx	1402xx27402xxx
Contact pitch	3,5 mm/3,81mm	5mm	5,08mm	7,50mm	10,16mm	15mm
No. of contacts	2 - 12 poles	2 - 12 poles	2 - 8 poles	2 - 4 poles	2 - 4 poles	2 - 4 poles
Rated surge voltage (III/2) ¹⁾	2,5 kV	4 kV	4 kV	6 kV	8 kV	8 kV
Rated surge voltage (III/2) ¹⁾	2,5 kV	4 kV	4 kV	6 kV	8 kV	8 kV
Rated surge voltage (III/3) ¹⁾	2,5 kV	4 kV	4 kV	6 kV	8 kV	8 kV
Rated Voltage	300 V	300 V	300 V	300 V	600 V	600 V
Rated voltage (II/2) ¹⁾	300 V	600 V	600 V	1000 V	1000 V	1000 V
Rated voltage (III/2) ¹⁾	150 V	300 V	300 V	600 V	1000 V	1000 V
Rated voltage (III/3) ¹⁾	150 V	220 V	300 V	400 V	1000 V	1000 V
Working current	12 A	13,5 A	17,5 A	17,5 A	60 A	135 A
Usegroup B, rated voltage / current	300 V / 12 A	300 V / 13,5 A	300 V / 17,5 A	300 V/17,5A	300 V / 60 A	600 V / 135 A
Usegroup C, rated voltage / current	- / -	- / -	- / -	150 V/17,5A	300 V / 60 A	600 V / 135 A
Usegroup D, rated voltage / current	300 V / 12 A	300 V / 13,5 A	300 V / 17,5 A	300 V/17,5A	600 V / 5 A	- / -
Contact resistance	max. 15 mOhm					
Insulation resistance	min. 10 ⁹ Ohm (500 V DC)					
Temperature range	-40°C ... +110°C					
Termination technology	THR Relfow					
PCB thickness	-	-	-	-	max. 2,4mm	max. 2,4mm
Insertion force	n.a					
Withdrawal force	n.a					
Hot plugging	No					
Mechanical Shock IEC 61373 (05/10)	5 g, 30 ms, 5 shocks/axis and each direction no contact disturbance >= 1µs					
Random Vibration IEC 61373 (05/10)	Cat 1 class B 5,72m/s ² no contact disturbance >=1µs					
RoHS - compliant	Yes					
UL file	E314677					

Isulator material

Material	PA/PPA
Color	black
Moisture Sensitivity Level (MSL)	1
UL classification	UL 94-V0
Material group acc. to IEC 60664-1	I (CTI > 600)


Contact material

Contact material	Copper alloy
Plating termination zone	Sn
Plating contact zone	Ni

Derating


The current carrying capacity is limited by maximum temperature of materials for inserts and contacts including terminals.
The current capacity curve is valid for continuous, non interrupted current loaded contacts of connectors when simultaneous power on all contacts is given, without exceeding the maximum temperature.

Control and test procedures according to DIN IEC 60512-5



¹⁾(overvoltage cat. / pollution degree)

Soldering instructions for lead-free tin soldering



Cable connection

Type	3,50/3,81 TTSH	5,00 TTSH 1,5mm ²	5,08 TTSH 2,5mm ²	7,50 TTSH	10,16 TTSH	15,00 TTSH
Part numbers	1402xx14402xxx 1402xx15402xxx	1402xx16402xxx	1402xx16404xxx	1402xx21404xxx	1402xx25402xxx	1402xx27402xxx
Conductor size AWG max	16 AWG	16 AWG	12 AWG	12 AWG	6 AWG	1 AWG
Conductor size AWG min	28 AWG	30 AWG	30 AWG	30 AWG	20 AWG	20 AWG
Conductor size solid max	1,5 mm ²	1,5 mm ²	2,5 mm ²	2,5 mm ²	16 mm ²	35 mm ²
Conductor size solid min	0,05 mm ²	0,05 mm ²	0,05 mm ²	0,05 mm ²	0,5 mm ²	0,5 mm ²
Conductor size stranded max	1 mm ²	1,0 mm ²	2,5 mm ²	2,5 mm ²	10 mm ²	25 mm ²
Conductor size stranded min	0,05 mm ²	0,05 mm ²	0,05 mm ²	0,05 mm ²	0,5 mm ²	0,5 mm ²
Conductor size stranded for end sleeve						
Stripping length max	6 mm	6 mm	6,5 mm	6,5 mm	11,5 mm	18 mm
Stripping length min	5 mm	5 mm	5,5 mm	5,5 mm	10,5 mm	18 mm
Screw thread	M2	M3	M3	M3	M4	M5
Tightening Torque max	0,25 Nm	0,6 Nm	0,6 Nm	0,6 Nm	1,5 Nm	2,5 Nm
Tightening Torque min	0,20 Nm	0,5 Nm	0,5 Nm	0,5 Nm	1,2 Nm	2,1 Nm

Packging unit

types 3.50/3.81/5.00/5.08 TTSH

Type of packaging	No. of poles (xx)	Quantity	Index (xxx)	Remark
box	2	300	000	
box	3	200	000	
box	4 - 5	150	000	
box	6 - 12	100	000	

types 7.50 TTSH

Type of packaging	No. of poles (xx)	Quantity	Index (xxx)	Remark
box	2	200	000	
box	3	150	000	
box	4	100	000	

type 10.16 TTSH

Type of packaging	No. of poles (xx)	Quantity	Index (xxx)	Remark
box	2 - 3	50	000	
box	4	40	000	

type 15.00 TTSH

Type of packaging	No. of poles (xx)	Quantity	Index (xxx)	Remark
box	2	50	000	
box	3	40	000	
box	4	30	000	

1402xx14402xxx



All Dimensions in mm
Original Size DIN A3

Scale
1:1

Free size tol.

Ref.

Sub.



All rights reserved

Department EL PD

Created by
ZHUANGJ

Inspected by
LUOK

Standardisation
302077

Date
2020-11-23

State
Final Release

har-flexicon terminal block horizontal, screwing

Doc-Key / ECM-Nr.
100542555/UGD/001/H
500000183169

HARTING Electronics GmbH

D-32339 Espelkamp

Type
DS

Number
14027301801

Rev.
H

Page
1/2


har-flexicon terminal block horizontal, screwing



Derating for solid wire 16mm² and 35mm²

The current carrying capacity is limited by maximum temperature of materials for inserts and contacts including terminals.
The current capacity curve is valid for continuous, non interrupted current loaded contacts of connectors when simultaneous power on all contacts is given, without exceeding the maximum temperature.

Control and test procedures according to DIN IEC 60512-5



No. of position 3

	All Dimensions in mm Original Size DIN A3	Scale 1:1		Free size tol.		Ref.	
						Sub.	
	All rights reserved	Created by ZHUANGJ	Inspected by LUOK	Standardisation 302077	Date 2020-11-23	State Final Release	
	Department EL PD	Title har-flexicon terminal block horizontal, screwing				Doc-Key / ECM-Nr. 100542555/UGD/001/H 500000183169	
HARTING Electronics GmbH D-32339 Espelkamp	Type DS					Number 14027301801	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

<u>14020816402000</u>	<u>14021016402000</u>	<u>14020216404000</u>	<u>14020316402000</u>	<u>14020316404000</u>	<u>14020414402000</u>
<u>14020416404000</u>	<u>14020516404000</u>	<u>14021214402000</u>	<u>14020416402000</u>	<u>14020516402000</u>	<u>14020814402000</u>
<u>14020216402000</u>	<u>14020616402000</u>	<u>14021014402000</u>	<u>14020214402000</u>	<u>14020314402000</u>	<u>14020614402000</u>
<u>14021216402000</u>	<u>14020914402000</u>	<u>14020514402000</u>	<u>14020714402000</u>	<u>14021114402000</u>	<u>14020427402000</u>
<u>14020227402000</u>	<u>14020327402000</u>	<u>14020325402000</u>	<u>14020225402000</u>	<u>14020425402000</u>	<u>14020916402000</u>
<u>14021116402000</u>	<u>14020716402000</u>	<u>14020315402000</u>	<u>14020215402000</u>	<u>14020515402000</u>	<u>14020715402000</u>
<u>14020615402000</u>	<u>14020816404000</u>	<u>14020815402000</u>	<u>14020415402000</u>	<u>14020716404000</u>	<u>14021215402000</u>
<u>14020616404000</u>	<u>14021015402000</u>	<u>14020915402000</u>	<u>14021115402000</u>	<u>14020214402333</u>	<u>14020314402333</u>
<u>14020316402333</u>	<u>14020316404333</u>	<u>14020216402333</u>	<u>14020216404333</u>	<u>14020414402333</u>	<u>14020416402333</u>