

GENERAL INFORMATION

No. of contacts	from 6 to 100poles, all even numbers
Contact spacing	1,27mm x 1,27mm [0,050"x0,050"]
Test Voltage	500V
Contact resistance	< 25 mOhm
Insulation resistance	≥ 10x10 ⁹ Ω
Working current acc. to IEC 60512, at 70°C, 80% derating	see derating diagram
Working temperature range	-55°C ... +125°C
Termination technology	IDC
Clearance & creepage distance	0,4mm min.
Insertion force (depending on mating connector)	approximately 0,5N/contact
Withdrawal force (depending on mating connector)	approximately 0,5N/contact
Mating cycles	PL1 : 500 mating cycles PL2 : 250 mating cycles
RoHS - compliant	Yes
Leadfree	Yes
Working voltage acc. to IEC 60664-1	100V / 150V (depending on installation category)
UL file acc. UL 1977	ECBT2.E102079
UL file acc. CSA-C22.2 (for Canada)	ECBT8.E102079

INSULATOR MATERIAL

Material	LCP (liquid crystalline polymer)
Color	Black
UL classification	UL94-V0
Material group acc. IEC 60664-1	IIIa (175 ≤ CTI < 400)


CONTACT MATERIAL

Contact material	Copper alloy
Plating termination zone	Sn
Plating contact sliding side	Au over PdNi (acc. to Performance level)


DERATING DIAGRAM acc. to IEC 60512-5 (Current carrying capacity)

The current carrying capacity is limited by maximum temperature of materials for inserts and contacts including terminals.
The current capacity curve is valid for continuous, non interrupted current loaded contacts of connectors when simultaneous power on all contacts is given, without exceeding the maximum temperature.

Control and test procedures according to DIN IEC 60512-5
derating curve at I_{max}*0,8 (IEC 60512-5-2)



CABLE ASSEMBLY REQUIREMENTS



FLAT CABLE REQUIREMENT FOR IDC CONNECTORS

PVC flat cables	AWG 30/1 (solid) AWG 30/7 (stranded)
PTFE flat cables	AWG 30/1 (solid)
Insulation diameter	min 0,55mm - max 0,75 mm

Important note :

For an undisturbed operation of the cable assembly, please use a har-flex IDC cable connector on both ends of the cable.
If you have to use a different cable connector beside one har-flex IDC cable connector, please, make sure to have the correct pin assignement of the ribbon cable wires according to this data sheets.

		All Dimensions in mm Original Size DIN A3		Scale 1:1	Free size tol.	Ref.		
						Sub.		
	All rights reserved			Created by ZHUANGJ	Inspected by LUOK	Standardisation KOHLE	Date 2017-10-13	State Final Release
	Department EC PD - CN							
	HARTING Electronics GmbH D-32339 Espelkamp				Title har flex female IDC			Doc-Key / ECM-Nr. 100578170/UGD/000/B 500000126530
Type DS					Number 15292100601		Rev. B	Page 1/2





har-flex female IDC





PACKAGING

2-5 fully filled connector trays (depending on pin counts) with optional strain relief bottom tray




Pin count	Number of trays	Connectors per tray	Connectors per package
6	2	65	130
8	2	55	110
10	2	50	100
12	2	50	100
14	2	45	90
16	3	40	120
18	3	40	120
20	3	35	105
22	3	35	105
24	4	30	120
26	4	30	120
28	4	30	120
30	4	25	100
32	4	25	100
34	4	25	100
36	4	25	100
38	5	20	100
40	5	20	100
42	5	20	100
44	5	20	100
46	5	20	100
48	5	20	100
50	5	15	75
52	5	15	75
54	5	15	75
56	5	15	75
58	5	15	75
60	5	15	75
62	5	15	75
64	5	15	75
66	5	15	75
68	5	15	75
70	5	10	50
72	5	10	50
74	5	10	50
76	5	10	50
78	5	10	50
80	5	10	50
82	5	10	50
84	5	10	50
86	5	10	50
88	5	10	50
90	5	10	50
92	5	10	50
94	5	10	50
96	5	10	50
98	5	10	50
100	5	10	50

OPTIONNAL STRAIN RELIEF



Pin count	E (mm)
6 to 58 pins	15
60 to 100 pins	16.2

Bottom tray for Strain relief



		All Dimensions in mm Original Size DIN A3		Scale 1:1		Free size tol.		Ref.							
								Sub.							
		All rights reserved Department EC PD - CN		Created by ZHUANGJ		Inspected by LUOK		Standardisation KOHLER		Date 2017-10-13		State Final Release			
				Title har flex female IDC								Doc-Key / ECM-Nr. 100578170/UGD/000/B 500000126530			
HARTING Electronics GmbH D-32339 Espelkamp				Type DS		Number 15292100601						Rev. B		Pag 2/	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

15290062502000	15290122502000	15290202502000	15290265502000	15290322502000	15290402502000
15290162502000	15290182501000	15290302502000	15290342502000	15290242502000	15290122501000
15290262501000	15290802501000	15290682501000	15290102502000	15290182502000	15290602501000
15290082502000	15291002502000	15291002501000	15290062501000	15290642502000	15290362501000
15290642501000	15290162501000	15290422502000	15290402501000	15290242501000	15290302501000
15290142502000	15290082501000	15290102501000	15290802502000	15290322501000	15290502501000
15290362502000	15290262502000	15290202501000	15290682502000	15290142501000	15290442502000
15290342501000	15290126501000	15290382501000	15290382502000	15290522501000	15290126502000
15290406501000	15290442501000	15290522502000	15290266502000	15290146501000	15290266501000
15290602502000	15290506501000				