



Pushing Performance  
Since 1945

# SEK-19 SV MA STD STR29 RLG 60P PL2 KINK



Image is for illustration purposes only. Please refer to product description.

Part number	09 19 560 6004
Specification	SEK-19 SV MA STD STR29 RLG 60P PL2 KINK

## Identification

Category	Connectors
Series	SEK Standard
Element	Male connector
Description of the contact	Straight Kinked

## Version

Termination method	Reflow soldering termination (THR)
Connection type	PCB to cable
Number of contacts	60
Termination length	2.9 mm
Locking type	With long levers

## Technical characteristics

Contact rows	2
Contact spacing (termination side)	2.54 mm
Rated current	1 A
Insulation resistance	>10 <sup>9</sup> Ω
Contact resistance	≤20 mΩ
Limiting temperature	-55 ... +125 °C (during reflow soldering max. +240 °C for 60 s)
Performance level	2 acc. to IEC 60603-13
Mating cycles	≥250

## Technical characteristics

Test voltage $U_{r.m.s.}$	1 kV
Isolation group	II ( $400 \leq CTI < 600$ )
PCB thickness	1.5 mm +0.44

## Material properties

Material (insert)	Thermoplastic resin (PCT)
Colour (insert)	Beige
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side Sn over Ni Termination side
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26


## Specifications and approvals

Specifications	IEC 60603-13
----------------	--------------

## Commercial data

Packaging size	1
ETIM	EC002637
eCl@ss	27460201 PCB connector (board connector)

## Cross section of solder termination



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09195606004](#)