



Pushing Performance  
Since 1945

# SEK-19 SV MA STD STR29 64P PLS4 KINK




Image is for illustration purposes only. Please refer to product description.

Part number	09 19 564 5024
Specification	SEK-19 SV MA STD STR29 64P PLS4 KINK

## Identification

Category	Connectors
Series	SEK Standard
Element	Male connector
Description of the contact	Straight Kinked

## Version

Termination method	Reflow soldering termination (THR)
Connection type	PCB to cable
Number of contacts	64
Termination length	2.9 mm

## Technical characteristics

Contact rows	2
Contact spacing (termination side)	2.54 mm
Rated current	1 A
Insulation resistance	$>10^9 \Omega$
Contact resistance	$\leq 20 \text{ m}\Omega$
Limiting temperature	-55 ... +125 °C (during reflow soldering max. +240 °C for 60 s)
Performance level	NM 30 (S4)
Mating cycles	$\geq 250$
Test voltage $U_{r.m.s.}$	1 kV
Isolation group	II ( $400 \leq CTI < 600$ )



**Pushing Performance**  
Since 1945

## Technical characteristics

PCB thickness	1.5 mm +0.44
---------------	--------------

## Material properties

Material (insert)	Thermoplastic resin (PCT)
Colour (insert)	Beige
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side Sn over Ni Termination side
Layer thickness	≥0.76 µm
Layer thickness	≥30 µinch
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 60603-13
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079


## Commercial data

Packaging size	1
ETIM	EC002637
eCl@ss	27460201 PCB connector (board connector)



**Pushing Performance**  
Since 1945

Cross section of solder termination



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09195645024](#)