

# Han B Hood Coupler LC 1 Lever M20



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| Part number        | 19 30 006 1750                                                                        |
| Specification      | Han B Hood Coupler LC 1 Lever M20                                                     |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19300061750">https://b2b.harting.com/19300061750</a> |

## Identification

|                          |                        |
|--------------------------|------------------------|
| Category                 | Hoods/Housings         |
| Series of hoods/housings | Han® B                 |
| Type of hood/housing     | Cable to cable housing |
| Type                     | Low construction       |

## Version

|                      |                                                   |
|----------------------|---------------------------------------------------|
| Size                 | 6 B                                               |
| Version              | Top entry                                         |
| Cable entry          | 1x M20                                            |
| Locking type         | Single locking lever                              |
| Han-Easy Lock®       | Yes                                               |
| Field of application | Standard hoods/housings for industrial connectors |

## Technical characteristics

|                                        |                                                |
|----------------------------------------|------------------------------------------------|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65                                           |
| Type rating acc. to UL 50 / UL 50E     | 4<br>4X<br>12                                  |

## Material properties

|                         |                    |
|-------------------------|--------------------|
| Material (hood/housing) | Aluminium die-cast |
|-------------------------|--------------------|



**Pushing Performance**  
Since 1945

## Material properties

|                                                            |                                                           |
|------------------------------------------------------------|-----------------------------------------------------------|
| Surface (hood/housing)                                     | Powder-coated                                             |
| Colour (hood/housing)                                      | RAL 7037 (dust grey)                                      |
| Material (seal)                                            | NBR                                                       |
| Material (locking)                                         | Polycarbonate (PC)<br>Stainless steel                     |
| Colour (locking)                                           | RAL 7037 (dust grey)                                      |
| Material flammability class acc. to UL 94 (locking levers) | V-0                                                       |
| RoHS                                                       | compliant                                                 |
| ELV status                                                 | compliant                                                 |
| China RoHS                                                 | e                                                         |
| REACH Annex XVII substances                                | Not contained                                             |
| REACH ANNEX XIV substances                                 | Not contained                                             |
| REACH SVHC substances                                      | Yes                                                       |
| REACH SVHC substances                                      | Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate |
| ECHA SCIP number                                           | 60b1a572-bb3f-476f-9307-b7d1688bd90c                      |
| California Proposition 65 substances                       | Yes                                                       |
| California Proposition 65 substances                       | Nickel<br>Naphthalene                                     |
| Fire protection on railway vehicles                        | EN 45545-2 (2020-08)                                      |
| Requirement set with Hazard Levels                         | R22 (HL 1-3)<br>R23 (HL 1-3)                              |

## Specifications and approvals

|           |                                                            |
|-----------|------------------------------------------------------------|
| UL / CSA  | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | CE<br>DNV GL                                               |

## Commercial data

|                                |               |
|--------------------------------|---------------|
| Packaging size                 | 1             |
| Net weight                     | 90 g          |
| Country of origin              | Germany       |
| European customs tariff number | 85389099      |
| GTIN                           | 5713140125209 |
| ETIM                           | EC000437      |



**Pushing Performance**  
Since 1945

## Commercial data

eCl@ss

27440202 Shell for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19300061750](#)